


# 3M™ Pin Strip Header

2 mm × 2 mm Solder Tail Straight & Right Angle, Surface Mount Straight

1512 Series



- Mates with a variety of dual row 2 mm board mount and wire mount sockets
- High temperature insulator compatible with lead-free solder processes
- Extensive pin count availability from 4 to 80 positions
- Available with vacuum cap in tape and reel packaging for automatic placement
- Minimizes use of PC board space
- End and side stackable design
- RoHS Compliant. See the Regulatory Information Appendix (RIA) in the “RoHS Compliance” section of [www.3Mconnectors.com](http://www.3Mconnectors.com) for compliance information (RIA E1 & C1 apply)

Date Modified: January 14, 2013

TS-0808-H  
Sheet 1 of 4

## Physical

### Insulation:

Material: Glass-filled LCP

Flammability: UL 94V-0

Color: Black

### Contact:

Material: Copper Alloy

### Plating:

Underplating: 50 μ" [1.27 μm] Nickel

Wiping Area: 30 μ" [0.76 μm] Gold Avg.

Solder Tails: 200-300 μ" [5.08-7.62 μm] Matte Tin

Marking: None

## Electrical

**Current Rating:** 3.50 A, 1 Line Powered

1.75 A, 6 Adjacent Lines Powered

1.00 A, All Lines Powered

Rating Conditions: EIA-364-070 Method 2, 30°C maximum temperature rise, 20% derated. Reference appropriate 3M Product Specification for detailed current derating curves.

**Insulation Resistance:**  $> 1 \times 10^9 \Omega$  at 250 V<sub>DC</sub>

**Withstanding Voltage:** 500 V<sub>RMS</sub> at Sea Level

## Environmental

**Temperature Rating:** -55°C to +105°C

**Process Rating:** Maximum 260°C (per J-STD-020C)

**Moisture Sensitivity Level:** 1 (per J-STD-020C)

UL File No.: E68080



Electronic Solutions Division  
Interconnect Solutions

<http://www.3Mconnectors.com>


3M is a trademark of 3M Company.  
For technical, sales or ordering information call  
**800-225-5373**

# 3M™ Pin Strip Header

2 mm × 2 mm Solder Tail Straight & Right Angle, Surface Mount Straight

1512 Series

## Straight



## Recommended Mounting Hole Pattern

## Pin Cross Section

| Contact Quantity | Dimension C  |
|------------------|--------------|
| 04               | 0.157 [4.0]  |
| 06               | 0.236 [6.0]  |
| 08               | 0.315 [8.0]  |
| 10               | 0.394 [10.0] |
| 12               | 0.472 [12.0] |
| 14               | 0.551 [14.0] |
| 16               | 0.63 [16.0]  |
| 18               | 0.709 [18.0] |
| 20               | 0.787 [20.0] |
| 22               | 0.866 [22.0] |
| 24               | 0.945 [24.0] |
| 26               | 1.024 [26.0] |
| 28               | 1.102 [28.0] |
| 30               | 1.181 [30.0] |
| 32               | 1.26 [32.0]  |
| 34               | 1.339 [34.0] |
| 36               | 1.417 [36.0] |
| 38               | 1.496 [38.0] |
| 40               | 1.575 [40.0] |
| 42               | 1.654 [42.0] |
| 44               | 1.732 [44.0] |
| 46               | 1.811 [46.0] |
| 48               | 1.89 [48.0]  |
| 50               | 1.969 [50.0] |
| 52               | 2.047 [52.0] |
| 54               | 2.126 [54.0] |
| 56               | 2.205 [56.0] |
| 58               | 2.283 [58.0] |
| 60               | 2.362 [60.0] |
| 80               | 3.15 [80.0]  |

mm  
[Inch]

| Tolerance Unless Noted |        |       |
|------------------------|--------|-------|
|                        | in.    | mm    |
| 0.X                    | -      | ±0.5  |
| 0.XX                   | ±0.01  | ±0.25 |
| 0.XXX                  | ±0.005 | ±0.13 |

[ ] Dimensions for Reference Only



## Ordering Information

**1512XX-8X22-RB** (RIA E1 & C1 Apply)

Contact Quantity  
(See Table 1)

Pin Length  
Dim 'A'  
3 = .130"  
4 = .152"

TS-0808-H  
Sheet 2 of 4



Electronic Solutions Division  
Interconnect Solutions  
<http://www.3Mconnectors.com>



3M is a trademark of 3M Company.  
For technical, sales or ordering information call  
**800-225-5373**

# 3M™ Pin Strip Header


2 mm × 2 mm Solder Tail Straight & Right Angle, Surface Mount Straight

1512 Series

## Right Angle



Recommended  
Mounting Hole Pattern



Pin Cross Section

| Contact Quantity | Dimension C  |
|------------------|--------------|
| 04               | 0.157 [4.0]  |
| 06               | 0.236 [6.0]  |
| 08               | 0.315 [8.0]  |
| 10               | 0.394 [10.0] |
| 12               | 0.472 [12.0] |
| 14               | 0.551 [14.0] |
| 16               | 0.63 [16.0]  |
| 18               | 0.709 [18.0] |
| 20               | 0.787 [20.0] |
| 22               | 0.866 [22.0] |
| 24               | 0.945 [24.0] |
| 26               | 1.024 [26.0] |
| 28               | 1.102 [28.0] |
| 30               | 1.181 [30.0] |
| 32               | 1.26 [32.0]  |
| 34               | 1.339 [34.0] |
| 36               | 1.417 [36.0] |
| 38               | 1.496 [38.0] |
| 40               | 1.575 [40.0] |
| 42               | 1.654 [42.0] |
| 44               | 1.732 [44.0] |
| 46               | 1.811 [46.0] |
| 48               | 1.89 [48.0]  |
| 50               | 1.969 [50.0] |
| 52               | 2.047 [52.0] |
| 54               | 2.126 [54.0] |
| 56               | 2.205 [56.0] |
| 58               | 2.283 [58.0] |
| 60               | 2.362 [60.0] |
| 80               | 3.15 [80.0]  |

mm  
[Inch]

| Tolerance Unless Noted |        |       |
|------------------------|--------|-------|
|                        | in.    | mm    |
| 0.X                    | -      | ±0.5  |
| 0.XX                   | ±0.01  | ±0.25 |
| 0.XXX                  | ±0.005 | ±0.13 |

[ ] Dimensions for Reference Only



## Ordering Information

**1512XX-7X22-RB** (RIA E1 & C1 Apply)

Contact Quantity  
(See Table 1)

Pin Length  
Dim 'A'  
3 = .130"  
4 = .152"

TS-0808-H  
Sheet 3 of 4





Electronic Solutions Division  
Interconnect Solutions  
<http://www.3Mconnectors.com>

3M is a trademark of 3M Company.  
For technical, sales or ordering information call  
**800-225-5373**

# 3M™ Pin Strip Header

2 mm × 2 mm Solder Tail Straight & Right Angle, Surface Mount Straight

1512 Series



Recommended PCB Pad Layout

Pin Cross Section



| Contact Quantity | Dimension C  | Tape Width | Order Code |
|------------------|--------------|------------|------------|
| 04               | 0.157 [4.0]  | n/a        | n/a        |
| 06               | 0.236 [6.0]  | n/a        | n/a        |
| 08               | 0.315 [8.0]  | 24 mm      | WB         |
| 10               | 0.394 [10.0] | 24 mm      | WC         |
| 12               | 0.472 [12.0] | 24 mm      | WC         |
| 14               | 0.551 [14.0] | 24 mm      | WC         |
| 16               | 0.63 [16.0]  | 24 mm      | WC         |
| 18               | 0.709 [18.0] | 32 mm      | WC         |
| 20               | 0.787 [20.0] | 32 mm      | WC         |
| 22               | 0.866 [22.0] | 44 mm      | WD         |
| 24               | 0.945 [24.0] | 44 mm      | WD         |
| 26               | 1.024 [26.0] | 44 mm      | WD         |
| 28               | 1.102 [28.0] | 44 mm      | WD         |
| 30               | 1.181 [30.0] | 44 mm      | WD         |
| 32               | 1.26 [32.0]  | 56 mm      | WE         |
| 34               | 1.339 [34.0] | 56 mm      | WE         |
| 36               | 1.417 [36.0] | 56 mm      | WE         |
| 38               | 1.496 [38.0] | 56 mm      | WE         |
| 40               | 1.575 [40.0] | 56 mm      | WE         |
| 42               | 1.654 [42.0] | 56 mm      | WE         |
| 44               | 1.732 [44.0] | 72 mm      | WF         |
| 46               | 1.811 [46.0] | 72 mm      | WF         |
| 48               | 1.89 [48.0]  | 72 mm      | WF         |
| 50               | 1.969 [50.0] | 72 mm      | WF         |
| 52               | 2.047 [52.0] | 72 mm      | WF         |
| 54               | 2.126 [54.0] | 72 mm      | WF         |
| 56               | 2.205 [56.0] | 72 mm      | WF         |
| 58               | 2.283 [58.0] | 88 mm      | WG         |
| 60               | 2.362 [60.0] | 88 mm      | WG         |
| 80               | 3.15 [80.0]  | n/a        | n/a        |

Notes: 1. Tape & reel include vacuum pick-up cap for pick n place handling equipment.  
2. Parts in tray packaging are supplied without vacuum cap.

| mm<br>[Inch]           |        |       |
|------------------------|--------|-------|
| Tolerance Unless Noted |        |       |
|                        | in.    | mm    |
| 0.X                    | -      | ±0.5  |
| 0.XX                   | ±0.01  | ±0.25 |
| 0.XXX                  | ±0.005 | ±0.13 |

[ ] Dimensions for Reference Only

## Ordering Information

**1512XX-2X20-RB-XX** (RIA E1 & C1 Apply)

Contact Quantity  
(See Table 1)

Pin Length  
Dim 'A'  
3 = .130"  
4 = .152"

Packaging suffix:  
Blank = Tray Packaging  
WX = Tape & Reel Packaging  
(see table 1)

TS-0808-H  
Sheet 4 of 4



Electronic Solutions Division  
Interconnect Solutions  
<http://www.3Mconnectors.com>

3M is a trademark of 3M Company.  
For technical, sales or ordering information call  
**800-225-5373**

3M is a trademark of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



### 3M Electronics Solutions Division

6801 River Place Blvd.  
Austin, TX 78726-9000  
U.S.A.  
1-800-225-5373  
[www.3m.com/interconnects](http://www.3m.com/interconnects)

Please recycle. Printed in USA.  
© 3M 2012. All rights reserved.  
RIA-2217B-E