Copyright FCI

FCIconnect.com

PRODUCT NUMBER
SEE TABLE



NOTES:

1. MATERIAL: GLASS FILLED POLYAMIDE.
   PART NUMBERS WITH A 'G' (963TC–NS12G) ARE A GRAYISH TAN AND MATCH THE 963T CONNECTORS.
   PART NUMBERS WITH AN 'R' (963TC–LS12R) ARE A BROWNISH RED AND MATCH THE 963T2 CONNECTORS.
2. PART NUMBERS WITH 'NS' (963TC–NS12G) HAVE NO STRAIN RELIEF TABS.
3. SEE APPLICATION SPECIFICATION GS–20–004 FOR INSTRUCTIONS ON ASSEMBLY OF COVERS TO 963T AND 963T2 CONNECTORS.
4. PRODUCT NUMBERS WITH AN LF SUFFIX MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS–22–008.
5. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDERING PROCESSES.

ltr	ecn no	dr	date
A	V81852	JRV	1998-10-20
B	V12588	LSS	2001-10-25
C	V05–0152	HTB	2005-03-04
D	V06–0195	HTB	2006-03-10
E	V06–0647	JRV	2006-07-06
F	V07–0134	HTB	2007-02-16
G	V08–0401	HTB	2008-12-12

sheet index	revision	G	G
	sheet	1	2

mat'l. code: SEE NOTE 1

surface: ASME Y14.5

tolerance: ASME Y14.5

tolerances unless otherwise specified: angles; linear

dr	J.R. VOLSTORF	1998-10-20
engr	J.R. VOLSTORF	1998-10-20
chr	J.R. VOLSTORF	1998-10-20
appd	J.R. VOLSTORF	1998-10-20

projection: INCH

scale 1:1

product family: FASTECH

title: 963TC COVERS FOR 963T & 963T2 CONN.

dwg no: A92KC4077

sheet 1 of 3

size: A4

type: CUSTOMER Drawing

form: A4mmXLc

PDM: Rev:G STATUS:Released Printed: Jan 09, 2009

Copyright FCI

FCIconnect.com

PRODUCT NUMBER NOTE 4	LUCENT DEVICE CODE	LUCENT COMCODE	"A"	"B"	"C"	"D"	"E"
963TC-NS6G	TCOV-NS6G	106904899	2	0.250	0.00	0.00	.00
963TC-NS6GLF	–	–	2	0.250	0.00	0.00	.00
963TC-NS8G	TCOV-NS8G	106904907	3	0.375	0.00	0.00	.00
963TC-NS8GLF	–	–	3	0.375	0.00	0.00	.00
963TC-NS12G	TCOV-NS12G	106904915	5	0.625	0.00	0.00	.00
963TC-NS12GLF	–	–	5	0.625	0.00	0.00	.00
963TC-NS16G	TCOV-NS16G	106904923	7	0.875	0.00	0.00	.00
963TC-NS16GLF	–	–	7	0.875	0.00	0.00	.00
963TC-NS20G	OBSOLETE						
963TC-NS20GLF	OBSOLETE						
963TC-NS24G	TCOV-NS24G	106904956	11	1.375	0.00	0.00	.00
963TC-NS24GLF	–	–	11	1.375	0.00	0.00	.00
963TC-NS12R	TCOV-NS12R	106904618	5	0.625	0.00	0.00	.00
963TC-NS12RLF	–	–	5	0.625	0.00	0.00	.00
963TC-NS20R	OBSOLETE						
963TC-NS20RLF	–	–	9	1.125	0.00	0.00	.00
963TC-NS24R	OBSOLETE						
963TC-NS24RLF	–	–	11	1.375	0.00	0.00	.00
963TC-LS6G	TCOV-LS6G	106905425	2	0.250	0.20	0.30	.48
963TC-LS6GLF	–	–	2	0.250	0.20	0.30	.48
963TC-LS8G	TCOV-LS8G	106905433	3	0.375	0.20	0.30	.48
963TC-LS8GLF	–	–	3	0.375	0.20	0.30	.48
963TC-LS12G	TCOV-LS12G	106905458	5	0.625	0.30	0.50	.48
963TC-LS12GLF	–	–	5	0.625	0.30	0.50	.48
963TC-LS16G	TCOV-LS16G	106905466	7	0.875	0.30	0.50	.48
963TC-LS16GLF	–	–	7	0.875	0.30	0.50	.48
963TC-LS20G	OBSOLETE						
963TC-LS20GLF	–	–	9	1.125	0.30	0.50	.48
963TC-LS24G	TCOV-LS24G	106905482	11	1.375	0.30	0.50	.48
963TC-LS24GLF	–	–	11	1.375	0.30	0.50	.48

mat'l. code: SEE NOTES	surface: ASME Y14.5	tolerance: ASME Y14.5	projection
ltr: G; ecn no; dr; date	tolerances unless otherwise specified		INCH
	angles; linear		scale 1:1
	dr: J.R. VOLSTORF 1998-10-20		
	engr: J.R. VOLSTORF 1998-10-20		
	chr: J.R. VOLSTORF 1998-10-20		
	appd: J.R. VOLSTORF 1998-10-20		
sheet index; revision sheet			

product family: FASTECH

title: 963TC COVERS FOR 963T & 963T2 CONN.

dwg no: A92KC4077 — sheet 2 of 3 — size A4

type: CUSTOMER Drawing

form: A4mmXLc

PDM: Rev:G STATUS:Released Printed: Jan 09, 2009

Copyright FCI

FCIconnect.com

PRODUCT NUMBER NOTE 4	LUCENT DEVICE CODE	LUCENT COMCODE	"A"	"B"	"C"	"D"	"E"
963TC-LS6R	OBSOLETE						
963TC-LS6RLF	–	–	2	0.250	0.20	0.30	.48
963TC-LS8R	OBSOLETE						
963TC-LS8RLF	OBSOLETE						
963TC-LS12R	TCOV-LS12R	106905359	5	0.625	0.30	0.50	.48
963TC-LS12RLF	–	–	5	0.625	0.30	0.50	.48
963TC-LS16R	OBSOLETE						
963TC-LS16RLF	–	–	7	0.875	0.30	0.50	.48
963TC-LS20R	OBSOLETE						
963TC-LS20RLF	–	–	9	1.125	0.30	0.50	.48
963TC-LS24R	TCOV-LS24R	106905391	11	1.375	0.30	0.50	.48
963TC-LS24RLF	OBSOLETE						
963TC-LE20RLF	–	–	9	1.125	0.60	0.80	.25
963TC-NS6G-CB	OBSOLETE						
963TC-NS8G-CB	OBSOLETE						
963TC-NS12G-CB	OBSOLETE						
963TC-NS16G-CB	OBSOLETE						
963TC-NS20G-CB	OBSOLETE						
963TC-NS24G-CB	OBSOLETE						
963TC-LS6G-CB	OBSOLETE						
963TC-LS8G-CB	OBSOLETE						
963TC-LS12G-CB	OBSOLETE						
963TC-LS16G-CB	OBSOLETE						
963TC-LS6R-CB	OBSOLETE						
963TC-LS8R-CB	OBSOLETE						
963TC-LS12R-CB	OBSOLETE						
963TC-LS16R-CB	OBSOLETE						
963TC-LS20R-CB	OBSOLETE						
963TC-LS24R-CB	OBSOLETE						

mat'l. code: SEE NOTES	surface: ASME Y14.5	tolerance: ASME Y14.5	projection
ltr: G; ecn no; dr; date	tolerances unless otherwise specified		INCH
	angles; linear		scale 1:1
	dr: T. BREWBAKER 2006-03-10		
	engr: T. BREWBAKER 2006-03-10		
	chr: T. BREWBAKER 2006-03-10		
	appd: T. BREWBAKER 2006-03-10		
sheet index; revision sheet			

product family: FASTECH

title: 963TC COVERS FOR 963T & 963T2 CONN.

dwg no: A92KC4077 — sheet 3 of 3 — size A4

type: CUSTOMER Drawing

form: A4mmXLc

PDM: Rev:G STATUS:Released Printed: Jan 09, 2009