



Dual Lock™ Reclosable Fasteners Trial Bags

TB3540 (250/250), TB3541/TB3542 (400/170)

TB3550 (250/250), TB3551/TB3552 (400/170)

TB3560 (250/250), TB3561/TB3562 (400/170)

TB3870 (250/250), TB3871/TB3872 (400/170)

TB4570, TB4575

Technical Data

June, 2010

Product Description

3M™ Dual Lock™ Reclosable Fasteners are positive locking, hidden fasteners designed for use in a variety of attachment solutions. They consist of continuous strips of polyolefin stems with a mushroom shaped top protruding up from the backing. When snapped together the mushroom shaped caps interlock producing a strong reliable fastener.

There are three different stem densities of these fasteners (170, 250 and 400) that refer to the approximate number of stems per square inch. By inter-locking different stem density combinations you can create the strength that suits your application--more total stems produces higher strength.

The Dual Lock reclosable fasteners can be mated in the following combinations of increasing closure strength: Type 170 to Type 250, Type 170 to Type 400, Type 250 to Type 250 and Type 250 to Type 400. We do not recommend using the type 170 to 170 because it does not have good strength. We do not recommend using the type 400 to 400 because it is too strong and may cause stems and heads to rip out when prying apart--rendering the fastener no longer reclosable.

There are a variety of pressure sensitive adhesives available with Dual Lock reclosable fasteners to cover most application needs. The pressure sensitive adhesive makes the Dual Lock reclosable fasteners easy to use. Simply remove the liner, place the Dual Lock reclosable fasteners, and apply firm, consistent pressure to assure good contact with the substrate you are adhering.

3M™ Dual Lock™ Reclosable Fasteners Trial Bags

Product Construction

NOTE: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Adhesive Type	Product Number	3M™ Dual Lock™ Reclosable Fastener Trial Bag Description	Dual Lock Color Adhesive Color	Engaged Thickness inches	Thickness Unmated Inches $\pm 15\%$	Liner Type Thickness	Full Roll Product Number
Rubber Based Adhesive	TB3540	250/250, 1 in. (25.4mm) x 10 ft. (3.05m), 1 mated strip per bag	Black/Black	0.23	0.14	5 mil White silicone treated Polyolefin	SJ3540
	TB3541/TB3542	400/170, 1 in. (25.4mm) x 10 ft. (3.05m), 1 strip of each, pre-mated per bag					SJ3541 (400) SJ3442 (170)
General Purpose Acrylic Adhesive	TB3550	250/250, 1 in. (25.4mm) x 10 ft. (3.05m), 1 mated strip per bag	Black/White	0.23	0.14	4 mil Clear silicone treated Polyolefin with Red Printing	SJ3550
	TB3551/TB3552	400/170, 1 in. (25.4mm) x 10 ft. (3.05m), 1 strip of each, pre-mated per bag					SJ3551 (400) SJ3552 (170)
Clear Acrylic Adhesive	TB3560	250/250, 1 in. (25.4mm) x 10 ft. (3.05m), 1 mated strip per bag	Clear/Clear	0.23	0.14	4 mil Clear silicone treated Polyolefin with Red Printing	SJ3560
	TB3561/TB3562	400/170, 1 in. (25.4mm) x 10 ft. (3.05m), 1 strip of each, pre-mated per bag					SJ3561 (400) SJ3562 (170)
Modified Acrylic Adhesive	TB3870	250/250, 1 in. (25.4mm) x 10 ft. (3.05m), 1 mated strip per bag	Black/Grey	0.24	0.14	5 mil Red silicone treated Polyolefin	SJ3870
	TB3871/TB3872	400/170, 1 in. (25.4mm) x 10 ft. (3.05m), 1 strip of each, pre-mated per bag					SJ3871 (400) SJ3872 (170)
Low Surface	TB4570 Clear	1 in. (25.4mm) x 10 ft. (3.05m), 1 mated strip per bag	Clear/Clear	0.098	0.065	6.5 mil 86# silicone treated Polycoated Kraft	SJ4570
	TB4575 Black	1 in. (25.4mm) x 10 ft. (3.05m), 1 mated strip per bag	Black/Clear				SJ4575

*All thickness values are with the liner removed.

3M™ Dual Lock™ Reclosable Fasteners Trial Bags

System Performance

Note: The following technical information and data is intended as a guideline to assist customers in selecting 3M™ Reclosable Fasteners for further evaluation. This technical information is not product release specifications or standards. Unless stated differently, the typical system performance and product properties were obtained using specific test methods under controlled laboratory conditions of 72°F ± 5°F and 50% ± 10% relative humidity. The user is responsible for evaluating 3M reclosable fasteners under expected use conditions to ensure suitable performance for the intended application.

Typical Test values for 3M™ Dual Lock™	type 170 to 250	type 170 to 400	type 250 to 250	type 250 to 400	Low Profile to Low Profile
Dynamic Tensile LbsF/in ² (N/cm ²) Engage Disengage	13 (9) 27 (18.5)	21 (14.5) 43 (29.6)	22 (15.2) 43 (29.6)	31 (21.4) 60 (41.4)	27 (18.5) 40 (27.5)
Dynamic Shear Lbs/in ²	14 (9.8)	21 (14.5)	22 (15)	59 (41.3)	41 (28.2)
Cleavage Strength Lbs/inch width (N/cm width) Rigid backed from Rigid backed	12 (21)	20 (35)	24 (42)	32 (56)	4 (7.1)
“T” Peel (Lbs/inch width (N/cm width) Flexible from flexible	0.7 (1.2)	1.4 (2.5)	1.9 (3.3)	1.5 (2.6)	0.5 (.9)
90° Peel lbs/inch width (N/cm width) Flexible from rigid	1.8 (3.2)	3.1 (5.4)	4.1 (7.2)	4.6 (8.1)	1.7 (2.9)
Cycle life # of closures before losing 50% of original strength	1000	1000	1000	1000	100

****Tests were run at 12 inches per minute****

3M™ Dual Lock™ Reclosable Fasteners Trial Bags

Product Performance

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

This guide should assist you in determining which product will adhere best to your substrate for your application.

3M™ Dual Lock™ Reclosable Fasteners Trial Bags	Poly-propylene (29) Low Surface Energy	Poly-ethylene (31)	Acrylic (38) Medium Surface Energy	PC (42)	ABS (42)	Aluminum (840) High Surface Energy	Stainless Steel (700-1100)	Temperature Resistance °F
TB3560 TB3561/TB3562 Clear Acrylic Adhesive			X	X	X	X	X	220
TB3550 TB3551/TB3552 General Purpose Acrylic Adhesive			X	X	X	X	X	200
TB3870 TB3871/TB3872 Modified Acrylic Adhesive			X	X	X	X	X	180
TB4570 Clear TB4575 Black LSE Acrylic #1	X	X	X	X	X	X	X	158
TB3540 TB3541/TB3542 Rubber Based Adhesive	X	X	X	X	X	X	X	120
	X-substrates that will typically adhere to without the use of primer							

Design Considerations

As a general rule, four square inches of fastener area per pound of static tensile or shear load to be supported is suggested as a starting point for evaluation. More or less area may be needed depending on specific conditions or end use applications. 3M™ Dual Lock™ Reclosable Fasteners Type 250 less than 0.75" (19 mm) width should not be engaged to other Dual Lock reclosable fastener type 250 because low disengagement values may occur.

Note

Final product performance depends upon a combination of factors: the substrate and its surface characteristics, the fastener selected, the application method and conditions, the time and environmental conditions required for the application. Because these factors are unique to each application, the user must evaluate the Dual Lock reclosable fastener and do any testing required to determine Dual Lock reclosable fasteners suitability for the end-user's application.

3M™ Dual Lock™ Reclosable Fasteners Trial Bags

Certification/ Recognition

MSDS: 3M has not prepared a MSDS for this product which is not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the product should not present a health or safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health or safety hazards.

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000 - ISO/TS 16949:2002

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 and ISO/TS 16949:2002 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M and Dual Lock are trademarks of 3M Company.
Printed in U.S.A.
©3M 2009 70-0709- 4051-8 (6/10)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[TB3540](#) [TB3541/TB3542](#) [TB3550](#) [TB3551/TB3552](#) [TB3560](#) [TB3561/TB3562](#) [TB3870](#) [TB3871/TB3872](#) [TB4570](#)
[TB4575](#)