



Volition™

Category 6 RJ45 Patch Cables



Category 6 RJ45 Patch Cable

Part of the 3M™ Volition Network Solutions these Category 6 patch cables allow you to complete your Category 6 system to EIA/TIA 568 or ISO 11801 Class E and EN 50173-1 Class E performance.

The RJ45 patch cables are available in either UTP or SSTP cable to ensure the appropriate electromagnetic compatibility protection level your customer requires

The patch cables are supplied in lengths of 0.5, 1, 2, 3, 4, 5, 7, 10, 12, 15 and 20 metre in the following configurations:

- Category 6 UTP PVC
- Category 6 UTP LSOH
- Category 6 SSTP LSOH

The patch cables comply with Flame Retardancy Standard IEC 60332-1.

LSOH versions are also compliant with IEC 60754-1 as required by the European Standard EN 50173.

Features

3M patch cables offer

- Optimization with 3M Volition RJ45 K6 jacks
- Moulded boot
- Available in 0.5, 1, 2, 3, 4, 5, 7, 10, 12, 15 and 20 metre lengths
- UTP and SSTP versions

Benefits

- offers best channel performance
- better mechanical protection ensures the minimum bend radius is not exceeded
- Flexibility to complete systems to your requirements
- Solutions for all levels of EMC protection

Specifications

Features

- 3M branded
- Category 6 link component
- Moulded boot
- 4 pairs of flexible multi-stranded copper conductors
- Polyethylene conductor insulation to NFC 32060
- Two types of outer jacket depending on use: PVC or zero halogen (LSOH*) material with flame retardant properties to IEC 60332-1




* compliant with Standard IEC 60754-1

For SSTP version

- Synthetic water-repellent tape.
- General shielding by copper braid
- Pair by pair shielding by aluminium/polyester tape

Ordering Information

Ref.-No.

	Volition™ Cat 6 RJ45 to RJ45 Patch Cable, UTP, PVC	
	Length	VOL-6UP-L0.5
	0.5 m	VOL-6UP-L1
	1.0 m	VOL-6UP-L2
	2.0 m	VOL-6UP-L3
	3.0 m	VOL-6UP-L4
	4.0 m	VOL-6UP-L5
	5.0 m	VOL-6UP-L7
	7.0 m	VOL-6UP-L10
	10.0 m	VOL-6UP-L12
	12.0 m	VOL-6UP-L15
	15.0 m	VOL-6UP-L20
	20.0 m	
	Volition™ Cat 6 RJ45 to RJ45 Patch Cable, UTP, LSOH	
	Length	VOL-6UL-L0.5
	0.5 m	VOL-6UL-L1
	1.0 m	VOL-6UL-L2
	2.0 m	VOL-6UL-L3
	3.0 m	VOL-6UL-L4
	4.0 m	VOL-6UL-L5
	5.0 m	VOL-6UL-L7
	7.0 m	VOL-6UL-L10
	10.0 m	VOL-6UL-L12
	12.0 m	VOL-6UL-L15
	15.0 m	VOL-6UL-L20
	20.0 m	
	Volition™ Cat 6 RJ45 to RJ45 Patch Cable, SSTP, LSOH	
	Length	VOL-6SSL-L0.5
	0.5 m	VOL-6SSL-L1
	1.0 m	VOL-6SSL-L2
	2.0 m	VOL-6SSL-L3
	3.0 m	VOL-6SSL-L4
	4.0 m	VOL-6SSL-L5
	5.0 m	VOL-6SSL-L7
	7.0 m	VOL-6SSL-L10
	10.0 m	VOL-6SSL-L12
	12.0 m	VOL-6SSL-L15
	15.0 m	VOL-6SSL-L20
	20.0 m	

Also available in Red, Blue, Yellow, Green

3M and Volition are trademarks of 3M. Quante is a trademark of Quante AG.

Important Notice

3M does not accept responsibility or liability, direct or consequential arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law.

If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price of the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.



3M Telecommunications

Europe, Middle East & North Africa
c/o Quante AG
Carl-Schurz-Straße 1 · 41453 Neuss · Germany

Tel.: ++49 (0)2131 / 14-5999
Fax: ++49 (0)2131 / 14-5998
Internet: www.3MTelecommunications.com