



Speed, Performance, Value - Perfect Balance

- 5 weighing units (kg, g, lb, oz, lb:oz)
- Automatic memory accumulation
- Pre-set counting with alarm
- Date and time
- Adjustable filters
- Full range tare
- Internal counting resolution 1:400,000
- Check-weighing with low and high limits
- Check weighing LED bar graph
- Capacity tracker
- Large backlit LCD display
- Overload protection
- Non-slip adjustable levelling feet
- Large stainless steel platform
- Pillar mounted
- Full colour coded keypad with numeric entry
- Precision load cell technology
- Simple user-friendly operation
- Splashproof to protect from accidental spills
- Easy access to the rechargeable battery
- RS-232 bi-directional interface
- External calibration
- Auto sleep / power down function to save battery life
- Low battery indication
- AC Adapter
- Weighing
- Parts counting
- Percentage weighing
- Animal / dynamic weighing
- Check weighing
- Check counting



Technical Specifications

Model	GFK 165aH	GFK 165a	GFK 330aH	GFK 330a	GFK 660a	GFK 1320a
Maximum capacity	165lb/75kg	165lb/75kg	330lb/150kg	330lb/150kg	660lb/300kg	1320lb/600kg
Readability	0.002lb/1g	0.01lb/5g	0.005lb/2g	0.02lb/10g	0.05lb/20g	0.1lb/50g
Pan size	15.7 x 19.7" / 400 x 500mm					23.6 x 31.5" / 600 x 800mm

General Specifications

Typical stabilisation time	2-3 Sec
Power supply	Internal rechargeable battery internal 230VAC or 120VAC 50/60Hz Transformer
Display	Backlit green display with 20mm digits and capacity tracker
Housing	ABS Plastic Indicator and Stainless Steel Pan
Overall dimensions (wxdxh)	15.7 x 24.4 x 33.9" / 400 x 620 x 860mm

Key Accessories

- In-use Cover
- RS-232 to PC Cable
- Adam DU - Data Collection Program
- RS-232 to USB Interface Cable (must be ordered in conjunction)
- ATP Thermal Printer
- Thermal Paper For Adam ATP (10 pack)



le)



Adam Equipment - offices worldwide

www.adamequipment.com