

Amphenol
FCI
© 2016 APCI

PRODUCT NUMBER
5 4 2 0 2 - X X X X X - X X X LF

PLATING
S=15μ"[0.38μm]
ON CONTACT AREA
100μ"[2.5μm]TIN
ON TAIL(NOTE 13)
G=30μ"[0.76μm]
ON CONTACT AREA
100μ"[2.5μm]TIN
ON TAIL(NOTE 13)
T=100μ"[2.5μm]TIN
ON CONTACT AREA
AND ON TAIL(SEE NOTE 11)
F=2μ"[0.05μm]GOLD
ON CONTACT AREA
AND ON TAIL

LEAD FREE OPTION NOTE 9 & 10

POLARIZATION
NOTE 6

PACKAGING TYPE, NOTE 5

POSITIONS PER ROW
02 TO 20



LEAD STYLE	POST	TAIL OVERALL WIDTH	PCB LAYOUT
06	0.177/4.50	.290 ^{+0.015} _{-0.017} / 7.37 ^{+0.38} _{-0.43}	FIGURE 1
08 30	0.230/5.84 0.318/8.08	.290 ^{+0.015} _{-0.017} / 7.37 ^{+0.38} _{-0.43}	FIGURE 1
60	0.575/14.60	.374 ^{+0.015} _{-0.017} / 9.50 ^{+0.38} _{-0.43}	FIGURE 2

NOTES:

- ① HOUSING MAT'L: HIGH TEMPERATURE THERMOPLASTIC.
FLAME RETARDANT PER UL 94V-0
COLOR: BLACK
OR
MINERAL FILLED LCP FLAME RETARDANT
PER UL-94V-0. COLOR: BLACK.
- THESE PART NUMBERS WILL WITHSTAND EXPOSURE
TO 260 C PEAK TEMPERATURE FOR 20 SECONDS IN
WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.




- ② PIN MATERIAL: PHOSPHOR-BRONZE
- ③ TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS ROW.
EXAMPLE: 10 POS., N x .100/2.54=1.00/25.4
- ④ 2LBS/0.9KG MIN. PIN RETENTION IN EITHER DIRECTION.
- ⑤ PACKAGING: NONE =POLY BAGS WITHOUT PICKUP CAP.
T =TUBES (OMIT DASH IF NOT POLARIZED).
P =TUBES WITH PICKUP CAPS.
A =TAPE AND REEL WITH PICKUP CAPS.
C =CUSTOMIZED TAPE AND REEL WITH PICKUP CAPS.
D =TAPE AND REEL WITHOUT PICKUP CAPS.
S =SPECIAL REQUEST OF TAPE AND REEL WITH PICKUP CAPS.
M =TAPE AND REEL WITH PICKUP CAPS FOR SPECIAL CUSTOMER.
- ⑥ FOR POLARIZATION, SPECIFY POSITION NUMBER
(i.e. A03=ROW A POS. 3) TO OMIT PIN.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
PRODUCT MANAGEMENT APPROVAL REQUIRED PRIOR TO RELEASE
OR SALE OF POLARIZED PRODUCTS.

7. UNDERPLATING: 50μ"/1.2μm Ni.
8. PIN TIPS ON Sn PLATED PRODUCT MAY HAVE BARE METAL ON TWO SIDES,
BOTH ENDS.
- ⑨ PART NUMBERS WITH "LF" SUFFIX AT THE END ARE LEAD FREE.
- ⑩ THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑪ "THIS PRODUCT HAS 100% PURE TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT
ENVIRONMENTS."
12. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW
OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- ⑬ MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION



mat'l. code NOTES 2 & 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family BERGSTIK
ltr	ecp no	dr	date	tolerances unless otherwise specified		scale 1:1	title
AA	ELX-N-21232	MZ	2015-06-25	angles	.XXX±01/.XX±0.3		.100 UNSHROUDED HDR
AB	ELX-N-22858	MZ	2015-12-22	linear	.XXX±005/.XX±0.13		DUAL ROW VERT. SMT.
AC	ELX-N-35783	MZ	2020-01-03	0°±2°	.XXXX±0020/.XXX±0.051		
				dr	D.INGRAM	1999-05-17	dwg no
				enrg	H.SUNDAY	1999-07-21	sheet 1 of 3
				chr	H.SUNDAY	1999-07-21	size
				appd	H.SUNDAY	1999-07-21	A3
sheet	revision	AC	AC	AC	AC		type
index	sheet	1	2	3	4		Product Customer Drawing

PRODUCT NUMBER
SEE SHEET 1



mat'l. code NOTES 2 & 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 1:1	title .100 UNSHROUDED HDR DUAL ROW VERT. SMT.
AC				angles	linear		
				0°±2°			
				dr	D.INGRAM	1999-05-17	dwg no
				enr	H.SUNDAY	1999-07-21	sheet 2 of 4
				chr	H.SUNDAY	1999-07-21	size
				appd	H.SUNDAY	1999-07-21	A3
sheet	revision						type Product Customer Drawing
index	sheet						



Amphenol
FCI

© 2016 AFCI



TAPE AND REEL PACKAGING

SIZE	LEAD STYLE 08 POST (0.230 [5.84])	LEAD STYLE 30 POST (0.318 [8.08])
2X2	YES	YES
2X3	YES	
2X4	YES	YES
2X5	YES	
2X6	YES	
2X7	YES	YES
2X8	YES	
2X9	YES	
2X10	YES	
2X11	YES	
2X12	YES	YES
2X13	YES	
2X14	YES	
2X15	YES	
2X16	YES	YES
2X17	YES	
2X18	YES	
2X19	YES	
2X20	YES	

Cross Reference



CORE RANGE	EXTENDED RANGE
54202-X08XXLF	95278-X01-XXLF
54202-X30XXLF	95278-X02-XXLF

TAPE AND REEL PACKAGING



CUSTOMIZED CARRIER TAPE
FOR 2x2,2x3,2x4,2x5 SIZE.
(SEE NOTE 5)

mat'l. code NOTES 2 & 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK							
ltr				ecn no		dr		date		tolerances unless otherwise specified		title					
AC										linear		INCH/MM		.100 UNSHROUDED HDR DUAL ROW VERT. SMT.			
										.XX±.01/.X±0.3		scale 1:1		dwg no			
										.XXX±.005/.XX±0.13		Amphenol FCI		sheet 3 of 4			
										.XXXX±.0020/.XXX±0.051				size			
														A3			
														type Product Customer Drawing			
sheet index				revision sheet													

[illegible]