




FCI P/N	QTY
59807-XXXX	XXX

SPECIFICATIONS	
INSERTION LOSS	0.5dB MAX
RETURN LOSS	55dB MIN
FIBER PROTRUSION	30mm MAX
APEX OFFSET	45um MAX
FIBER UNDERCUT	SEE TELECARDIA QR-326



NOTES:
1. FCI PART NUMBER CONSISTS OF THE DVG NO, A DASH
A SUFFIX XXXX WHERE Y IS THE UNIT OF LENGTH (Y=H IS
METERS AND Y=F IS FEET) AND WHERE XXX IS THE LENGTH "L".
(EX. 59807-F004 IS 4 FEET IN LENGTH)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI Electronics	
ltr	ech no	dr	date	linear	NOMINALS ONLY	projection	title	product family	code
A	V11393	JLK	7/5/01		UNLESS NOTED		CA, SC-SC, 1.6mm ZIP SM-8.3	FIBER OPTICS	213
				angles					
				dr	J. KILE	7/5/01			
				engr	G. WARNER	7/5/01			
				chr	G. WARNER	7/5/01			
				opnd	G. WARNER	7/5/01			
sheet	revision	A							
index	sheet	1							

1 2

ACAD

3

code code
22526

4