




Tous droits strictement réservés. Reproduction ou communication à des tiers
interdite sans autorisation écrite de FCI B.V.
© FCI B.V.

All rights strictly reserved. Reproduction or issue to third parties in any form
whatever is not permitted without written authority from the proprietor.
© FCI B.V.

PRODUCT NUMBER see sheet 2 of 2



SECTION V-V



VIEW A-A

NOTES:


1. MATERIAL HOUSING: MODIFIED POLYPHENYLENE OXIDE (NORYL), COLOUR: BLACK, MEETING UL-94-V0.
2. RECOMMENDED PIN LENGTH IS 6.76 ± 0.25
3. MIN PULL OUT FORCE OF TERMINAL IS 28.5 Newton
4. TO REMOVE TERMINAL, PUSH TERMINAL FORWARD AND LIFT LATCH DAMAGE TO LATCH CAN OCCUR IF LIFTED MORE THAN A 25° ANGLE TO TOP OF HOUSING
5. FOR MAX CRIMPING INFORMATION SEE VIEW A-A FOR CORRECT CRIMP HEIGHT SEE JUMBO PV TERMINAL PR. 173 (TA-297)
6. THIS HOUSING IS INTENDED FOR USE WITH BERG JUMBO PV TERMINAL
7. ALL MARKING FOR MILITARY P/N'S ARE TO BE PER MIL-STD-1285 SEE TABULATION SHEET 2
8. MIL-PARTS 1x2, 1x3 AND 1x4 ARE TO SHORT FOR MIL-PART MARKING. MARK BAG ONLY.

mat'l. code see note 1				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS www.fciconnect.com	
ltr	ecn	no	dr	date	linear	projection	title	product family	code
A	0606	LNA	770509				jumbo latch	BERGCON	213
B	J90014	EMU	891128				HSG single row		
C	V11688	MM	910610		angles				
D	C20041	MM	920605	dr	M.Visschers	910617			
E	V41802	DDb	950110	engr	M.Loman	950110			
F	V90992	HME	990615	chr	M.Loman	910618			
G	F00405	VIB	000516	appd					
sheet	revision	G	B			scale	A2	65112	sheet
index	sheet	1	2			5:1			1 of 2

Tous droits strictement réservés. Reproduction ou communication à des tiers
interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
© FCI B.V.

All rights strictly reserved. Reproduction or issue to third parties in any form
wherever is not permitted without written authority from the proprietor.
© FCI B.V.

PRODUCT NUMBER	No OF POS.	DIM J	DIM K
65112-002	1 x 2	5.08	8.68
65112-003	1 x 3	10.16	13.76
65112-004	1 x 4	15.24	18.84
65112-005	1 x 5	20.32	23.92
65112-006	1 x 6	25.40	29.00
65112-007	1 x 7	30.48	34.08
65112-008	1 x 8	35.56	39.16
65112-009	1 x 9	40.64	44.24
65112-010	1 x 10	45.72	49.32
65112-011	1 x 11	50.80	54.40
65112-012	1 x 12	55.88	59.48
65112-013	1 x 13	60.96	64.56
65112-014	1 x 14	66.04	69.64
65112-015	1 x 15	71.12	74.72
65112-016	1 x 16	76.20	79.80
65112-017	1 x 17	81.28	84.88
65112-018	1 x 18	86.36	89.96
65112-019	1 x 19	91.44	95.04
65112-020	1 x 20	96.52	100.12



MILITARY PRODUCT NUMBER	MADE OF	MARKING STYLE	DESC P/N	CAGE NO.
65112-002 -MIL	65112-002	NOTE 8	86039-02	22526
65112-003 -MIL	65112-003	NOTE 8	86039-03	22526
65112-004 -MIL	65112-004	NOTE 8	86039-04	22526
65112-005 -MIL	65112-005	A	86039-05	22526
65112-006 -MIL	65112-006	A	86039-06	22526
65112-007 -MIL	65112-007	A	86039-07	22526
65112-008 -MIL	65112-008	A	86039-08	22526
65112-009 -MIL	65112-009	A	86039-09	22526
65112-010 -MIL	65112-010	A	86039-10	22526
65112-011 -MIL	65112-011	A	86039-11	22526
65112-012 -MIL	65112-012	A	86039-12	22526
65112-013 -MIL	65112-013	A	86039-13	22526
65112-014 -MIL	65112-014	A	86039-14	22526
65112-015 -MIL	65112-015	A	86039-15	22526
65112-016 -MIL	65112-016	A	86039-16	22526

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr	no	dr	date	linear	projection	title	www.fciconnect.com	
A	V11688	MM		910610			jumbo latch		
B	V41802	DD	B	950110			HSG single row		
					angles				
			dr	M.Visschers	910617		product family	BERGCON	code
			engr	M.Loman	950110		size	dwg no	213
			chr	M.Loman	910618		scale		sheet
			appd				A2	65112	2 of -
sheet index	revision	sheet							