










PRODUCT NO.
SEE TABLE



DIM 'C'
REF
SOLDER TAIL



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	.XX ±.01		
P	V11058	JM	6/12/91		.XXX ±.005	projection	title QUICKIE P.C.B. CONNECTOR 10,14,26,30,34, & 50 POS.
R	V50805	LSS	7/5/95		.XXXX ±.0020	INCH/MM	
S	N05-0123	ZC	5/9/05	angles	0° ±2°	scale	product family size dwg no
T	N07-0199	WG	08/27/07	dr	J.MUSTARD 6/12/91	2.5:1	
				enr	M.SMYK 6/12/91		code —
				chr	W.FUNK 6/12/91		
				appd	M.SMYK 6/12/91		sheet 1 of 2
sheet index	revision sheet	T	T				
		1	2				

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de©FCI ELECTRONICS. Droits de reproduction FCI ELECTRONICS INC.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of©FCI ELECTRONICS Copyright FCI ELECTRONICS INC.

	1	2								3		4
	NO. OF POS.	DIM "A"	DIM "B"	DIM "C" REF	SEE NOTE							
65495-017(LF)	10	. 450/11. 43	. 700/17. 78	. 100/2. 54	1							
-018(LF)					2							
-019(LF)					1							
-020(LF)					2							
-021(LF)	26	1. 250/31. 75	1. 500/38. 10	. 100/2. 54	1							
-022(LF)					2							
-023(LF)					1							
-024(LF)					2							
-025(LF)	34	1. 650/41. 91	1. 900/48. 26	. 100/2. 54	1							
-026(LF)					2							
-027(LF)					1							
-028(LF)					2							
-029(LF)	50	2. 450/62. 23	2. 700/68. 58	. 100/2. 54	1							
-030(LF)					2							
-031(LF)					1							
-032(LF)					2							
-033(LF)	14	. 650/16. 51	. 900/22. 86	. 100/2. 54	1							
-034(LF)					2							
-035(LF)					1							
-036(LF)					2							
-037(LF)	30	1. 450/36. 83	1. 700/43. 18	. 100/2. 54	1							
-038(LF)					2							
-039(LF)					1							
65495-040(LF)					2							

NOTES:

- ① 50u"/1.27uM MIN. Ni UNDERPLATE OVER ENTIRE TERMINAL. AND Au FLASH ON SOLDER TAIL ONLY.
- ② 65495-***: 150u"/3.81uM MIN. TIN/LEAD 93/7 OVER ENTIRE TERMINAL. 50u"/1.27uM MIN. Ni UNDERPLATE.
65495-***LF: 150u"/3.81uM MIN. MATTE TIN OVER ENTIRE TERMINAL. 50u"/1.27uM MIN. Ni UNDERPLATE.
- ③ SEE TA 247 FOR MORE INFORMATION.
- 4. PATTERN SHOWN FOR CENTER TEN CONTACTS IS TYPICAL FOR ALL CONNECTOR LENGTHS, EXCEPT 14 & 30 POSITIONS.
- 5. SUB-ASSEMBLY & COVER PACKED SEPARATELY.
- 6. THE HOUSING OF XXXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX ±.01/.0±.3	projection	title		
T					.XXX ±.005/.00±.13		QUICKIE P.C.B CONNECTOR		
					.XXX ±.0020/.000±.051		10,14,26,30,34,& 50 POS.		
				angles	0° ±2°		product family		
				dr	J.MUSTARD 6/11/91	INCH/MM	size		code
				enr	M.SMYK 6/11/91		dwg no		—
				chr	W.FUNK 6/11/91	scale	A		sheet
				appd	M.SMYK 6/11/91	1:1	65495		2 of
sheet index	revision sheet	T	2						