



PRODUCT NO.

SEE TABLE


ULTRASONIC WELD AREA

MFG SITE CODE

NOTE 6




VIEW B-B




NOTE 4

0.25 MIN



SECTION A-A




mat'l. code				surface	tolerance	projection	product family	
				ISO1302	ISO1101 ISO406		MOD JACK	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
H	ELX-N-16190	Henry	11/01/13	angles	0.X±0.3	mm	MODIFIED LOW PROFILE PCB III	
-	-	-	-	0°±2°	0.XX±0.15		HORZ MOD JCAK FOR 1.66mm P.C.B	
C	V60576	GAH	03/22/96		0.XXX±0.05	scale 1.0	dwg no	
D	T00076	BKB	3/30/00	dr	DKLIN	7/6/94	sheet, 1 of 2	
E	V00698	CSP	4/18/00	engr	TONY CHIEN	7/6/94	94908	
F	V03-1103	PJ	10/22/03	chr	TONY CHIEN	7/6/94	type	
G	V05-0187	LP	3/23/05	appd	JENN TSAO	7/6/94	Product Customer Drawing	
sheet	revision	H						
index	sheet	1						

PRODUCT NUMBER	NO. OF POS	LOADED POSITION
94908-X88	8	ALL POS.
94908-X86		2,3,4,5,6,7
94908-X84		3,4,5,6
94908-X84A		1,2,3,6
94908-X88LF	8	ALL POS.
94908-X86LF		2,3,4,5,6,7
94908-X84LF		3,4,5,6
94908-X84ALF		1,2,3,6


NOTE: PLEASE CHECK FOR AVAILABILITY,
NOT ALL OPTIONS AVAILABLE.

PLATING CODE	PLATING	HSG COLOR
0	5u" Au + high performance lubricant	BLACK
1	15μ" AU	
2	20μ" GFPD	
3	30μ" AU	
4	15μ" G.X.T	
5	50μ" AU	



WIRE POSITION No

P. C. B. HOLE PATTERN VIEWED FROM TOP.



NOTES:

1. RECOMMENDED P.C.B THICKNESS 1.60 MM
2. HOUSING MAT'L: NYLON 66, 25% GLASS REINFORCED, UL94-V0, COLOR : SEE TABLE.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREES C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MIN THICK CIRCUIT BOARD.
3. CONTACTS: PHOS BRONZE ALLOY UNS-C51000, 0.460 DIA. ROUND WIRE. SEE TABLE FOR PLATING.
4. PROTRUDED SHELF ONLY APPEARS ON 8-POS JACK.
5. STANDARD PACKAGING METHOD (USE TUBE): SEE GES-14-361. PACKAGING OF LEAD FREE PRODUCTS MEETS LABELING AND PACKAGING SPECIFICATION GS-14-920.
6. COMPANY LOGO LOCATED IN THIS AREA ,AND WOULD APPEAR IN THE SAME SHIPMENT UNLESS LOGO SPEC HEREIN IS UPDATED.
7. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection mm	product family MOD JACK
ltr	ecn no	dr	date	title
H				MODIFIED LOW PROFILE PCB III
				HORZ MOD JCAK FOR 1.60mm P.C.B
				dwg no
				94908
				sheet, 2 of 2
				size
				A4
				type
				Product Customer Drawing
sheet index	revision sheet	H	1	