







Threaded UNC 4.40 SELLERS

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	G±0.25
09	30.81	24.99	16.96	16.79	10.96	5.90
15	39.14	33.32	25.18	25.12	19.18	5.90
25	53.03	47.04	39.12	38.84	33.12	5.70
37	69.32	63.50	55.68	55.30	49.68	5.70



SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A6GV00LF	D09P24A6GV00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A6GV00LF	D15P24A6GV00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A6GV00LF	D25P24A6GV00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A*GV00LF	D37P24A*GV00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

V =SCREWLOCK Threaded UNC 4.40 sellers

4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —

SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A*GI00LF	D09P24A*GI00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A*GI00LF	D15P24A*GI00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A*GI00LF	D25P24A*GI00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A*GI00LF	D37P24A*GI00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.


I =SCREWLOCK Threaded M3

4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —


GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views



rev	ecn no	dr	date
A	-	BAR	2003/04/16
B	LS05-001	MPE	2005/03/14
C	LS05-0056	LGO	2005/07/07
D	LS06-0097	LGO	2006/07/28
E	I09-0268	NG	2009-11-24
F	I10-0059	NG	2010-02-23
-	-	-	-

www.fciconnect.com				surface		ISO 1302		✓	tolerance std		ISO 406 ISO 1101		projection			mm	
				TOLERANCES UNLESS OTHERWISE SPECIFIED													
Dr	JARRY	1995/08/11	ANGULAR	LINEAR		0.X	±0.1	size	A3	Scale		2					
Eng	PESSON	1995/08/11				0.XX	±0.1					ECN	I10-0059				
Chr	NIRMAL GEORGE	2010-02-23	0.XX	±2°		0.XXX	±0.1										
Appr	SUDHIR VARMA	2010-02-23	Product family		D-SUB		Spec ref		-								
FCI			title				HEADER DELTA D STD EUROPE				no		dwg		C01-8646-0816		Rev.
			HEADER DELTA D STD EUROPE														F
catalog no							-		CUSTOMER		sheet		1 of 1				