





-I max	7.5A
-Contact resistance	≤7.3mΩ
-Insulation resistance	≥5000MΩ
-TEST VOLTAGE	
contact/contact	≥1000V
contact/ground	≥1200V

-Contact force	≥0.20N
-Retention force	≥40N
-Insertion force	according
-Withdrawal force	according
-Mechanical endurance	:200 mat

- Material shell
- Material insulator
- Material contacts
- Finish on contact area
- Finish on termination end
- Solderability
- Shock
- Vibration

-Climatic category	-55° / +125°/21
-Corrosion	salt spray:24h



Dimensions are in millimeters

Shell size	Number of contacts	A +0.76 0	B +0.25 0	C ±0.12	F +0.51 0	G	H 0	K Maxi	L +0.22 0	Part number			
										0.4μ gold	0.76μ gold	1.25μ gold	flash gold
E	09	30.43	16.79	24.99	10.47	5.90 ^{+0.15}	19.02	1.50	0.80	DEF09PTX	DEF09P043TX	DEF09P052TX	DEF09P031TX
A	15	38.76	25.12	33.32	10.47	5.90 ^{+0.15}	27.25	1.50	0.80	DAP15PTX	DAP15P043TX	DAP15P052TX	DAP15P031TX
B	25	52.65	38.84	47.04	10.43	5.70 ^{+0.25}	41.02	1.50	0.80	DBP25PTX	DBP25P043TX	DBP25P0502TX	DBP25P031TX
C	37	68.94	55.30	63.50	10.56	5.70 ^{+0.25}	57.45	1.50	1.00	DCP37PTX	DCP37P043TX	DCP37P0502TX	DCP37P031TX

d	04/04/03	Add part number Flash gold.			
ISS	DATE	Latest modification by : JARRY		MOD N°	
Designed by: JOUBERT		date 27/02/95		Type of drawing: CLIENT	
TITLE : PIN CONNECTORS D SUB WITH SOLDER CONTACTS				SHEET 01	
SCALE: 1.5					
		FRAMATOME CONNECTORS FRANCE Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. 33 (16) 43.84.08.43			
		This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing from the owners		PROJECT	
FORMAT		SOURIAU DRG N°		M94D001	
A3		C01-8637-0446			

