

- Quick Links**
- [RoHS/LF P/N Search](#)
- Documentation**
- [Customer drawing search](#)
- [Free search](#)
- Services**
- [Distributor list](#)

Start > Search=UHC1200BRZ* > UHC1200-BRZ

UHC1200-BRZ

UHC1200-BRZ : Hylok Receptacle



Customer drawing

ACTIVE

[Add to Favorites](#)

[Print Datasheet](#)

FCI Brings You More

- [✉ Contact our sales/technical support](#)
- [📄 Sample request](#)

Specifications

[Download document](#)

General Dimensional Electrical Mechanical Physical Environmental Other Features

General	
Product Type	Terminal system
Terminal size (in mm)	Ø2
Family	Hylok
Features	Selective Gold plated versions available Split pin version for low-force mating Dual-locking lances
Dimensional	
Wire size range Min - Max	0.5 - 2.0 mm ²
Pitch	6.35 mm
Electrical	
Current Carrying Capacity at 23°C	15A
Maximum Insulation (in mm)	3.3
Resistance (Contact)	< 2 mohms
Mechanical	
Contact mating force	< 7N
Single Wire Seal Compatible	No
Contact unmating force	< 4N
Physical	
Plating	Sn
Material	CuZn
Environmental	
IMDS	No
Other Features	
Market	Passenger Vehicles
Type	Female
Tradename	Hylok
Disclaimer	Displayed data is for information purposes only. For more information, please contact your local sales office. The supply of some products might be limited to some customers.