




- VDC: 12, 24
- RPM: 2800~9500
- CFM: 2.70~10.61
- Impeller: 5 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 36g




## DC FAN

40x40x20mm

### Specification

|           | Bearing                                              | Voltage | Current    | Speed     | Input Power | Air Flow  | Static Pressure       | Noise     | Weight |
|-----------|------------------------------------------------------|---------|------------|-----------|-------------|-----------|-----------------------|-----------|--------|
| MODEL NO  | ○ Sleeve<br>● One ball and one sleeve<br>○ Hydraulic | (Vdc)   | (Amp)      | (Rpm)     | (Watts)     | (CFM)     | (mm/H <sub>2</sub> O) | dB(A)     | Gram   |
| B4020B12L | ●                                                    | 12      | 0.07       | 5000      | 0.84        | 5.43      | 3.35                  | 25.3      | 36     |
| B4020B12M | ●                                                    | 12      | 0.13       | 6500      | 1.56        | 7.01      | 5.90                  | 30.9      | 36     |
| B4020B12H | ●                                                    | 12      | 0.17       | 8000      | 2.04        | 9.33      | 9.31                  | 33.9      | 36     |
| C4020B12L | ●                                                    | 12      | 0.07       | 5000      | 0.84        | 5.43      | 3.35                  | 25.3      | 36     |
| C4020B12M | ●                                                    | 12      | 0.13       | 6500      | 1.56        | 7.01      | 5.90                  | 30.9      | 36     |
| D4020B12L | ●                                                    | 12      | 0.08       | 5000      | 0.96        | 5.43      | 3.35                  | 25.3      | 36     |
| D4020B12M | ●                                                    | 12      | 0.13       | 6500      | 1.56        | 7.01      | 5.90                  | 30.9      | 36     |
| D4020B24M | ●                                                    | 24      | 0.05       | 6500      | 1.20        | 7.01      | 5.90                  | 30.9      | 36     |
| D4020B24U | ●                                                    | 24      | 0.10       | 9500      | 2.40        | 10.61     | 12.21                 | 37.8      | 36     |
| E4020B12H | ●                                                    | 12      | 0.05~0.165 | 2800~9000 | 0.6~1.98    | 2.70~9.84 | 1.07~11.31            | 23.0~39.2 | 36     |
| F4020B12L | ●                                                    | 12      | 0.07       | 5000      | 0.84        | 5.43      | 3.35                  | 25.3      | 36     |
| F4020B12M | ●                                                    | 12      | 0.10       | 6500      | 1.20        | 7.01      | 5.90                  | 30.9      | 36     |
| F4020B12H | ●                                                    | 12      | 0.17       | 8600      | 2.04        | 9.83      | 10.59                 | 34.2      | 36     |
| F4020B12U | ●                                                    | 12      | 0.25       | 9500      | 3.00        | 10.61     | 12.21                 | 37.8      | 36     |

Design specifics subject to change without notice.



### STATIC PRESSURE

