




- MAT'L:
- 1.CABLE:UL2919,3COAXIAL+7C+1+AL/MY+BRAID,0.D:8.5
 - 2.CONNECTORS:HD15M,9th EMPTY,BLACK
 - 3.THUMBSCREW:#4-40UNC,E32
 - 4.BLACK HEAT SHRINK:ø1.5 X 15:6PCS
 - 5.COPPER SIZE:30 X 50
- NOTE:
- 1.TOTAL LENGTH:10000±50mm
 - 2.COLOR:BEIGE
 - 3.MOLDED TYPE
 - 4.360° SOLDER
 - 5.ROHS COMPLIANT

CONFIGURATION:

1	RED(COAX.)	1	RED(COAX.)
2	RED(GROUND)	2	RED(GROUND)
3	GREEN(COAX.)	3	GREEN(COAX.)
4	GREEN(GROUND)	4	GREEN(GROUND)
5	BLUE(COAX.)	5	BLUE(COAX.)
6	BLUE(GROUND)	6	BLUE(GROUND)
7	BROWN	7	BROWN
8	BLACK	8	BLACK
9	GREEN	9	GREEN
10	RED	10	RED
11	ORANGE	11	ORANGE
12	WHITE	12	WHITE
13	YELLOW	13	YELLOW
14	(BRAID)	14	(BRAID)
15	SHIELD	15	SHIELD

RoHS
Compliant

DATE	15 JAN,1999	PARTS NO	MN3073N	TITLE:	HD15 MALE-HD15 FEMALE	NO.	THUMBSCREW:#4-40UNC,E32	4
UNIT	MM	DRAWN NO	000240		(MOLDED TYPE)	②	#28,UL2919,3COAX+7C+1+AL/MY+B,0.D:8.5 10M	1
SCALE		BUYER NO	002		AK3750X 10M	①	HD15M,9th EMPTY,BLACK	1
					ASSMANN ELECTRONICS,INC.	DESCRIPTION		
						Y.C.C	CHECK	APPRO
						1/15		