


ISDN S-INTERFACE TRANSFORMERS


TM0048

MECHANICAL



Dimensions are in inches (mm) +/- .010(.254) unless noted otherwise.

SCHEMATIC



ELECTRICALS @ 25° C

Part Number	Turns Ratio (Pri:Sec) +/-2%	Unbalanced I _{DC} (mA MAX)	OCL Primary (mH MIN)	L _L Sec (uH)	C _{ww} (pF MAX)	C _D (pF MAX)	DCR (ohms +/-25%)		Schematic
							Pri	Sec	
0559-6200-06	1:2CT	5	22	15max	60	80	3.0	5.5	B
0559-6200-07	1:1	5	22	5max	40	40	2.8	2.7	A
0559-6200-08	1:2	5	22	15max	60	80	3.0	5.5	A
0559-6200-09	1:2.5	5	22	8 - 40	40	110	3.0	7.0	A
0559-6200-10	1:2	5	22	11max	50	110	2.8	5.5	A

3000 Vrms Isolation Voltage

Corporate Office

Bel Fuse Inc.
 198 Van Vorst Street, Jersey City, NJ 07302-4496
 Tel: 201-432-0463
 Fax: 201-432-9542
 E-Mail: BelFuse@belfuse.com
 Internet: http://www.belfuse.com

Far East Office

Bel Fuse Ltd.
 8F/8 Luk Hop Street
 San Po Kong
 Kowloon, Hong Kong
 Tel: 852-2328-5515
 Fax: 852-2352-3706

European Office

Bel Fuse Europe Ltd.
 Preston Technology Management Centre
 Marsh Lane, Preston PR1 8UD
 Lancashire, U.K.
 Tel: 44-1772-556601
 Fax: 44-1772-888366