

## GEWG

### Multi Loose Tube Cables

### Universal – Indoor / Outdoor - Galvanized Steel Wire Armor (SWA)

### A/I-DF(ZN)HBH

Full Rodent Protection

## Ordering Information

### Belden European Part Numbers

| Fibre type / count                    | 6                        | 12      | 24      | 36      |
|---------------------------------------|--------------------------|---------|---------|---------|
| 62.5/125-OM1                          | GEWG106                  | GEWG112 | GEWG124 | GEWG136 |
| 50/125-OM2 BW 600/1200                | GEWG206                  | GEWG212 | GEWG224 | GEWG236 |
| 50/125-OM3                            | GEWG306                  | GEWG312 | GEWG324 | GEWG336 |
| 50/125-OM2e                           | GEWG406                  | GEWG412 | GEWG424 | GEWG436 |
| 50/125-OM2 BW 500/500                 | GEWG506                  | GEWG512 | GEWG524 | GEWG536 |
| 50/125-OM4                            | GEWG606                  | GEWG612 | GEWG624 | GEWG636 |
| 9/125 ITU G.655                       | GEWG706                  | GEWG712 | GEWG724 | GEWG736 |
| 9/125 ITU G.652D                      | GEWG806                  | GEWG812 | GEWG824 | GEWG836 |
| Std. plywood reel<br>(non-returnable) | Ø 1250 * 688 mm<br>93 kg |         |         |         |
| Std. delivery length                  | 2100 ± 100m              |         |         |         |


## Applications

- For **outdoor** use in structured (data) wiring systems such as (**campus backbone**).
- For **outdoor** use in networks for telecom, cable TV and/or broadcast.
- Easy to install in ducts, tunnels and trenches by means of compressed air or pulling wire.
- Suitable for direct burial (crush ≤ 400 N/cm).

## Features & Benefits

- **High mechanical and full rodent protection** provided by Steel Wire **Armor (SWA)**.
- **Predicted lifetime > 30 years.**

## Construction & Dimensions



### Cable Specifications (construction in accordance with IEC 60794)

1. Dielectric central element of glass reinforced plastic (GRP), also as protection against kinks, surrounded by swelling yarns.
2. Jelly filled (non-dripping and silicon-free) loose tubes with primary coated optical fibres ( $\varnothing 250 \pm 15 \mu\text{m}$ ).  
Individually colour coded optical fibres: red – green – blue – yellow – violet – pink .
3. The loose tubes are stranded around the central element, if necessary with fillers (PE-natural).  
Colour coding of the loose tubes: 1. red – 2. green – rest white.
4. Jelly filling compound between interstices, and PET foil over cable core.
5. Swellable (for the longitudinal watertightness) aramid yarns as strength members.
6. Black UV resistant FRNC/LSNH inner jacket.
7. Steel Wire Armouring (SWA): helically stranded galvanized steel wires of  $\varnothing 0.9 \text{ mm}$
8. Black UV resistant FRNC/LSNH outer jacket.

Identification: BELDEN OFC – “cable type” – “number x fibre type” + date-, meter- and P/N marking.

## Mechanical Data

| No. of fibres                             | Max. 36     |
|-------------------------------------------|-------------|
| Cable core                                | 6 tubes     |
| $\varnothing$ Central element (mm)        | 1.9         |
| $\varnothing$ Loose tube (mm)             | 1.9         |
| $\varnothing$ Inner jacket nom./max. (mm) | 9.0 / 9.3   |
| $\varnothing$ Outer jacket nom./max. (mm) | 13.5 / 13.8 |
| Energy of flame (kJ/m)                    | 3300        |
| Weight (kg/km)                            | 330         |

## Optical Characteristics

Characteristics (cabled) Single-Mode – Matched-Cladded optical fibres according to ITU.

| European Partnumber Coding, Position 5 | Fibre-Type   | Mode-Field /Cladding Diameter (um) | Wave-length (nm) | Attenuation average/ max. (dB/km) | Dispersion (ps/(nm·km)) | PMD (ps/km)        | Cable Cut-off Wave-length (nm) |
|----------------------------------------|--------------|------------------------------------|------------------|-----------------------------------|-------------------------|--------------------|--------------------------------|
| 8                                      | 9/125 G.652D | 9.2 ± 0.4<br>125 ± 0.7             | 1310<br>1550     | 0.32 / 0.40<br>0.21 / 0.30        | ≤ 3.5<br>≤ 18           | ≤ 0.2              | ≤ 1260                         |
| 7                                      | 9/125 G.655  | 8.4 ± 0.6<br>125 ± 1               | 1550             | 0.25 / 0.30                       | 3.5 – 8.5               | ≤ 0.1 <sup>A</sup> | ≤ 1260                         |

Note A- Link design value

Characteristics (cabled) Multi-Mode Graded-Index optical fibres according to IEC 60793

| European Partnumber Coding, Position 5 | Fibre-Type   | Mode-Field Diameter (um) | Wave-length (nm) | Attenuation average/ max. (db/km) | Bandwidth (MHz·km) | Ethernet Performance (m) |             | Num. Apert. (μm) | Refr. Index    |
|----------------------------------------|--------------|--------------------------|------------------|-----------------------------------|--------------------|--------------------------|-------------|------------------|----------------|
|                                        |              |                          |                  |                                   |                    | 1GBE                     | 10 GBE      |                  |                |
| 1                                      | 62.5/125 OM1 | 62.5 ± 2.5<br>125 ± 1    | 850<br>1300      | 2.7 / 3.2<br>0.6 / 1.1            | ≥ 200<br>≥ 600     | 275<br>550               | 33<br>n.a.  | 0.275 ± 0.015    | 1.495<br>1.490 |
| 5                                      | 50/125 OM2   | 50 ± 2.5<br>125 ± 1      | 850<br>1300      | 2.4 / 3.0<br>0.7 / 1.0            | ≥ 500<br>≥ 500     | 600<br>600               | 82<br>n.a.  | 0.20 ± 0.015     | 1.481<br>1.476 |
| 2                                      | 50/125 OM2   | 50 ± 2.5<br>125 ± 1      | 850<br>1300      | 2.3 / 2.8<br>0.6 / 0.9            | ≥ 600<br>≥ 1200    | 600<br>600               | 82<br>n.a.  | 0.20 ± 0.015     | 1.481<br>1.476 |
| 4                                      | 50/125 OM2e  | 50 ± 2.5<br>125 ± 1      | 850<br>1300      | 2.3 / 2.8<br>0.6 / 0.9            | ≥ 600<br>≥ 1200    | 750<br>2000              | 110<br>na   | 0.20 ± 0.015     | 1.481<br>1.476 |
| 3                                      | 50/125 OM3   | 50 ± 2.5<br>125 ± 1      | 850<br>1300      | 2.5 / 3.0<br>0.5 / 1.0            | ≥ 1500<br>≥ 500    | 900<br>550               | 300<br>n.a. | 0.20 ± 0.015     | 1.482<br>1.477 |
| 6                                      | 50/125 OM4   | 50 ± 2.5<br>125 ± 1      | 850<br>1300      | 2.5 / 3.0<br>0.5 / 1.0            | ≥ 6000<br>≥ 500    | 900<br>550               | 550<br>n.a. | 0.20 ± 0.015     | 1.482<br>1.477 |

A test report (attenuation) is supplied with each delivery.

## Mechanical, Physical and/or Environmental Characteristics

| Requirements                                                                                                 |                                                   |
|--------------------------------------------------------------------------------------------------------------|---------------------------------------------------|
| <b>Temperature range</b> according to IEC 60794-1-2-F1<br>Transport/storage<br>Installation<br>Operation     | -30 to + 70 °C<br>-5 to + 50 °C<br>-30 to + 70 °C |
| <b>Pulling tension</b> according to IEC 60794-1-2-E1<br>Long term<br>Short term                              | ≤ 3000 N<br>≤ 6000 N                              |
| <b>Bending radii for fibres and tubes</b><br>Installation/operation                                          | >25 mm                                            |
| <b>Watertightness</b> according to IEC 60794-1-2-F5                                                          | Yes                                               |
| <b>Crush resistance</b> according to IEC 60794-1-2-E3<br>Cable                                               | ≤ 50 KN/m                                         |
| <b>Bending radii cable</b><br>Static according to IEC 60794-1-2-E11<br>Dynamic according to IEC 60794-1-2-E6 | 15 x Ø<br>20 x Ø                                  |
| <b>Flame retardancy</b> according to<br>IEC 60332-3-22 (EN 50266-2-2)<br>IEC 61034 (EN 50268)                | Pass<br>Pass                                      |
| <b>Halogen-free</b> according to IEC 60754-2 (EN 50267-2-2)<br>Corrosivity                                   | pH ≥ 3.5 - µS/cm ≤ 100                            |

## Guide to installation and handling

- When laying and installing optical fibre cables it is **vitaly important not to exceed the specified values** set for pulling tension, bending radii and temperature. The installation methods have to be in accordance with the common standards.
- To ease insertion into tubes by means of compressed air or pulling wire, certified lubricants (e.g. paraffin) may be used. The use of soap or similar substances as lubricants is strictly prohibited.
- If a cable needs to be fastened, constrictions > 0.3 mm must be prevented.
- The jelly filling inside the tubes can be removed using a tissue soaked in turpentine.
- It is advisable to cap the cable-ends during storage.

## Options

- Cables for outdoor use.
- **Non-standard cable constructions**, colors, details and/or additional information regarding specifications are available on request.

## Revision

| Rev.             | Description                           | Date                        | Init. |
|------------------|---------------------------------------|-----------------------------|-------|
| 2.0              | Remove Circuit Integrity IEC 60331-25 | 23/05/12                    | SN    |
|                  |                                       |                             |       |
|                  |                                       |                             |       |
|                  |                                       |                             |       |
| Date: 22/11/2010 |                                       | Part Number:<br><b>GEWG</b> |       |
| Page 1 of 1      |                                       |                             |       |
| Orig.: SN        |                                       | Review:                     |       |