



Large Cabinet Racks Economizer



Design Features

Welded Frame: 14-gauge steel vertical rails. 16-gauge steel top and bottom. Uniquely designed, 16-gauge steel rail supports. Furnished complete with removable sides, rear door and one pair of panel mounting rails.

Panel Mounting Rails: 12-gauge steel. Fully adjustable, tapped #10-32 in front on E.I.A. universal spacing. (Use #7346 screws - order separately) Separate .28 diameter holes provided for mounting accessories.

Side Panel: 20-gauge steel. Removable from outside for easy access.

Bottom: Pierced for RC-7758 casters, and with one 9.56 square hole and four 1.11 knock outs for cable access.

1200# Equipment load capacity.

Bonus Features

Finishes




Sand Texture (S), Royal Blue Texture (RB), and Black Texture (BT) are standard.
Available in other Bud textured finishes at no extra cost.

Economizer Racks with 19" Panel Width											
Non-Ventilated			Ventilated			Panel Space PS	Outside Height A	Outside Width B	Outside Depth C	Clear Inside Depth D	Weight (Lbs.)
Catalog Number	Accessories	Drawings	Catalog Number	Accessories	Drawings						

ER-16502			ER-16602			42.00"	47.31"	22.00"	18.50"	17.00"	110
ER-16503			ER-16603			52.50"	57.81"	22.00"	18.50"	17.00"	124
ER-16504			ER-16604			61.25"	66.56"	22.00"	18.50"	17.00"	139
ER-16505			ER-16605			70.00"	75.31"	22.00"	18.50"	17.00"	151
ER-16506			ER-16606			78.75"	84.06"	22.00"	18.50"	17.00"	163
ER-16511			N/A	N/A	N/A	21.00"	25.31"	22.00"	25.50"	24.00"	94
ER-16512			ER-16612			42.00"	47.31"	22.00"	25.50"	24.00"	128
ER-16513			ER-16613			52.50"	57.81"	22.00"	25.50"	24.00"	145
ER-16514			ER-16614			61.25"	66.56"	22.00"	25.50"	24.00"	162
ER-16515			ER-16615			70.00"	75.31"	22.00"	25.50"	24.00"	175
ER-16516			ER-16616			78.75"	84.06"	22.00"	25.50"	24.00"	189
ER-16521			N/A	N/A	N/A	21.00"	25.31"	22.00"	30.75"	29.25"	109
ER-16522			ER-16622			42.00"	47.31"	22.00"	30.75"	29.25"	143
ER-16523			ER-16623			52.50"	57.81"	22.00"	30.75"	29.25"	160
ER-16524			ER-16624			61.25"	66.56"	22.00"	30.75"	29.25"	180
ER-16525			ER-16625			70.00"	75.31"	22.00"	30.75"	29.25"	194
ER-16526			ER-16626			78.75"	84.06"	22.00"	30.75"	29.25"	209

- NOTES:**
- ① PANEL MOUNTING RAILS TAPPED #10-32 ON E.I.A. UNIVERSAL SPACING AND ARE FULLY ADJUSTABLE.
 - ② MOUNTING HOLES PIERCED IN BASE FOR #RC-7758 CASTERS.
 - ③ LOAD RATING: 1200 LBS. MAX.
- ☒ (2) SETS OF (10) HOODED LOUVERS CENTERED ON EACH SIDE.
☐ (2) SETS OF (15) HOODED LOUVERS CENTERED ON EACH SIDE.
☐ (4) SETS OF (10) HOODED LOUVERS ON EACH SIDE.
☐ (4) SETS OF (15) HOODED LOUVERS ON EACH SIDE.

MOUNTING PROVISIONS FOR OPTIONAL FAN.




MATERIAL:

SIDES AND REAR DOOR	20 GA. STEEL
REAR DOOR STIFFENER	18 GA. STEEL
TOP, BOTTOM, RAIL SUPPORTS AND DOOR STOPS	16 GA. STEEL
VERTICAL RAILS	14 GA. STEEL
PANEL MOUNTING RAILS	12 GA. STEEL

FINISH:

FRAME ASSEMBLY, SIDES AND REAR DOOR	SAND TEXTURE
	ROYAL BLUE TEXTURE
	BLACK TEXTURE
PANEL MOUNTING RAILS AND DOOR STOPS	SMOOTH BLACK



							OPTIONAL ACCESSORIES	
PART NO.	PANEL SPACE A	B	C	D	E	F	PANEL MTG. RAILS PART NO.	PLEXIGLAS DOORS PART NO.
ER-16602 ☒	42.000	47.312	18.500	17.000	—	38.562	PMR-9450	V-9063-A
ER-16603 ☐	52.500	57.812			—	49.062	PMR-9451	V-9064-A
ER-16604 ☐	61.250	66.562			27.531	57.812	PMR-9452	V-9065-A
ER-16605 ☐	70.000	75.312			31.906	66.562	PMR-9453	V-9066-A
ER-16606 ☐	78.750	84.062	18.500	17.000	36.281	75.312	PMR-9454	V-9067-A
ER-16612 ☐	42.000	47.312	25.500	24.000	—	38.562	PMR-9450	V-9063-A
ER-16613 ☐	52.500	57.812			—	49.062	PMR-9451	V-9064-A
ER-16614 ☐	61.250	66.562			27.531	57.812	PMR-9452	V-9065-A
ER-16615 ☐	70.000	75.312			31.906	66.562	PMR-9453	V-9066-A
ER-16616 ☐	78.750	84.062	25.500	24.000	36.281	75.312	PMR-9454	V-9067-A
ER-16622 ☐	42.000	47.312	30.750	29.250	—	38.562	PMR-9450	V-9063-A
ER-16623 ☐	52.500	57.812			—	49.062	PMR-9451	V-9064-A
ER-16624 ☐	61.250	66.562			27.531	57.812	PMR-9452	V-9065-A
ER-16625 ☐	70.000	75.312			31.906	66.562	PMR-9453	V-9066-A
ER-16626 ☐	78.750	84.062	30.750	29.250	36.281	75.312	PMR-9454	V-9067-A