

PART NAME	NON-METALLIC ENCLOSURE (STYLE B)	PART No.	NBB-10240 & NBB-10260 & NBB-15240	REV. DATE	7-23-14
-----------	----------------------------------	----------	-----------------------------------	-----------	---------

MATERIAL:

UL LISTED INDOOR VERSION

SOLID BODY & COVER _____ ABS/PC BLENDED PLASTIC
UL94-5VA FLAMMABILITY RATING

CLEAR COVER _____ POLYCARBONATE PLASTIC
UL94V-0 FLAMMABILITY RATING
UV STABILIZED

UL LISTED OUTDOOR VERSION

SOLID BODY & COVER _____ PBT/PC BLENDED PLASTIC
UL94-5VA FLAMMABILITY RATING
UV STABILIZED

ALL VERSIONS

GASKET _____ MODIFIED POLYURETHANE

FINISH:

BODY _____ LIGHT GRAY
COVER _____ LIGHT GRAY OR CLEAR


LATCHES & HINGES _____ NON-METALLIC
WALL MOUNTING BRACKETS _____ STAINLESS STEEL

NOTE: UNIT COMES COMPLETE WITH (4) WALL
MOUNTING BRACKETS & (4) M4x0.7 x 8mm LG.
TRUSS HEAD MACHINE SCREWS (NOT SHOWN)



COVER INCLUDES GRAY POLYURETHANE GASKET.

INDUSTRY STANDARDS:

UL508-4X TYPE 1, 4 AND 4X
NEMA TYPE 1, 4 AND 4X
IEC529-IP66



VIEW LESS COVER



DIMENSIONS = INCHES
[MILLIMETERS]

NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE
UNLESS OTHERWISE SPECIFIED

AIR AND MOISTURE VENTS, GALVANIZED STEEL AND
PLASTIC INTERNAL PANELS ARE NOT INCLUDED,
BUT CAN BE PURCHASED SEPARATELY.

UL LISTED INDOOR VERSION		UL LISTED OUTDOOR VERSION	DIMENSIONS													
PART NO.		PART NO.														
SOLID COVER	CLEAR COVER	SOLID COVER	A	B	C	D	E	F	G	H	J	K	L	M	N	P
NBB-10240	NBB-10260	NBB-15240	5.904 [150]	5.040 [128]	4.606 [117]	4.322 [110]	5.904 [150]	5.040 [128]	4.606 [117]	4.322 [110]	2.753 [70]	0.815 [21]	5.330 [135]	5.255 [133]	5.330 [135]	5.255 [133]