

YAEV26-L2


BURNDY® PRODUCTS

YAEV26-L2

YAEV26-L2 : 2/0 NYLON HVY DTY RING 5



ACTIVE

[Assistant](#)[Add to Favorites](#)
[✉ Email Datasheet](#)
[🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)
[📄 > Sample request](#)
[€ > Price request](#)

Specifications

[Download document](#)

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Strip length (Wire)			13/16 in.
Stud Hole (Size)			5/16 in.
Tongue Angle			Straight
Tongue Width (in)			0.93 in.
Wire Shroud			No
Insulation Diameter (Max)			0.628 in.
Physical			
Conductor Size			2/0 AWG
Conductor Type			Commercial/Military Stranded Copper
Insulation Type			Nylon
Color Code			Yellow
Conductor Size (Range)			2/0 AWG
Approvals / Certifications			
Military Listed			MS15036-135
UL Listed			No
CSA Certified			No
Military Specification			Class 1
Other Features			
Tongue Type			Ring
Bulk Catalog Number			Same
UPC			78181002760
Keyword			smtermHD