



The LuxemBright® Flare™ LED system is a low voltage, highly efficient alternative to traditional neon and fluorescent lighting. It offers easy installation, durability, and a long life span for all of your channel letter illumination needs. The 3 LED per module cluster design allows for extremely bright and homogenous lighting. Designed for signage applications with returns 3.0" or greater.

APPLICATIONS

- Channel Letters
- Front-lit and halo-lit
- Cove/accent lighting
- Cabinet box signs
- Backlighting
- Architectural lighting
- 3.5-5.0" return depths


BENEFITS

- Warranty up to 5 years
- Environmentally safe, RoHS compliant
- Energy efficient
- Easy to install
- UL Recognized (E332228)
- Modules are potted to IP67 standards

FEATURES

- Vibration resistant
- Operates on a 12 volt DC system
- Superior outdoor performance
- Cut and splice anywhere between modules
- Double-sided VHB tape on the back of each module
- Available in white, red, amber, green, and blue.






SPECIFICATIONS

COLOR	PRODUCT #	LM/FT.	MOD/FT.	VIEWING ANGLE	WATTS/MOD.	WATTS/FT.	WNTY (YEARS)	CCT/λ	40 w	60 w	120 w	240 w
WHITE 9000K	774-W0023	55	3	120	0.18	0.54	5	9000K	74	111	222	444
WHITE 6500K	774-W0025	55	3	120	0.18	0.54	5	6500K	74	111	222	444
WHITE 5000K	774-W0026	50	3	120	0.18	0.54	5	5000K	74	111	222	444
WHITE 3000K	774-W0024	50	3	120	0.18	0.54	5	3000K	74	111	222	444
RED	774-R0023	18	3	120	0.22	0.66	5	625NM	60	90	180	360
BLUE	774-B0023	6	3	120	0.18	0.54	5	470NM	74	111	222	444
GREEN	774-G0023	35	3	120	0.18	0.54	5	525NM	74	111	222	444
AMBER	774-Y0023	18	3	120	0.18	0.54	5	590NM	74	111	222	444
ORANGE	774-E0023	15	3	120	0.18	0.54	5	605NM	74	111	222	444

12 VDC POWER SUPPLIES

PRODUCT #	WATTS	OUTPUT VOLTAGE	MAX OUTPUT	INPUT VOLTAGE	INPUT CURRENT	 us	UL CLASS
771-14012	40	12 VDC	3.3 A	100-240, 277 VAC	0.5 A @ 100-240 VAC, 0.2 A @ 277 VAC	E249377	2
771-16112	60	12 VDC	5.0 A	100-240	1.2 A @ 115 VAC, 1 A @ 230 VAC	E320521, E307078	2
771-16212	60	12 VDC	5.0 A	100-240, 277 VAC	0.8 A @ 100-240 VAC, 0.3 A @ 277 VAC	E320521, E307078, E334687	2
771-17212	120*	12 VDC	10 A***	100-240, 277 VAC	2.5 A @ 90 VAC	E328880	2
771-18212	240**	12 VDC	20 A***	100-240, 277 VAC	3 A @ 115 VAC	E328880	2

* (2) 60 Watt Channels
 ** (4) 60 Watt Channels
 *** 5 A each channel



CAO LIGHTING, INC.
 LED through Innovation™

4628 West Skyhawk Drive, West Jordan, UT 84084-4501, USA
 Phone 877.236.4401 Fax 801.256.9287
www.LuxemBright.com



ISO 9001 CERTIFIED
 TS 16949 CERTIFIED FACTORY
 Patents Pending

Distributed By: