



Specifications

- Certifications*: UL, CSA, VDE
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon
- Bezel Material: Nylon

Dimensional Specifications: in. [mm]



			
TERMINAL TYPE			



T	A	20	1	-	T	B	-	B
SERIES	RATING¹		TERMINATION/FUNCTION					ACTUATOR COLOR³
T SINGLE POLE	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC					.250 SOLDER TAB (QC)	.187 TAB (QC)	B BLACK W WHITE
CIRCUIT	11 5A 250VAC 10A 125VAC 5A (TUNGSTEN) 125VAC L		FUNCTION	LUG			WIRE LEAD	
A ON-NONE-OFF			ON-NONE-OFF	0	1	3	5	
B ON-NONE-ON			(ON)-NONE-OFF	A	B	D	F	
C ON-OFF-ON			ON-NONE-(OFF)	L	M	R	T	
			ON-NONE-ON	0	1	3	5	B BLACK W WHITE
	20 10A 250VAC 15A 125VAC 3/4HP 125-250VAC		ON-NONE-(ON)	A	B	D	F	
			ON-OFF-ON	0	1	3	5	
	22 10A 250VAC 15A 125VAC 20A 125-250VAC H 3/4HP 125-250VAC							
	25 10A 250VAC 16A 125VAC 1/2HP 125-250VAC							
								ACTUATOR STYLE²
								P PADDLE
								PL PLUNGER
								PS PADDLE - SHORT
								T ROCKER
								TL MOMENTARY ROCKER

NOTES:

Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "Bezel" to the end of the catalog number. (ex.) TA201-TB-B/BEZEL

Imprinting is available. Please specify when ordering. (ex. TA201-TB-B/ON-OFF)

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

- 1 Rating Code 22 is 20A 125VAC inductive when momentary function is specified. Rating Code 22 only available with circuits A & B. Rating Code 25 only available with PL-Plunger actuator.
- 2 PL-Plunger actuator available only in T Series with circuit A, termination/function B or F, and terminals at T1 and 2.
- 3 Custom colors are available. Consult factory.