

MultiBoard USB

G81-7000 / G81-8000

Multifunctional, programmable USB keyboards with integrated Magnetic Stripe Reader. For commercial use and all other applications requiring a versatile and robust keyboard fulfilling the highest expectations to alphanumeric data entry. G81-7000 with space-efficient 405 mm width.



MultiBoard USB G81-7000



MultiBoard USB G81-8000



Facts & Features

- Single mechanical keys (Cherry FTSC Technology)
- Designed for continuous use - > 50 Mio key presses
- Robust and reliable
- Programmable Magnetic Stripe Reader
- Optional integrated Barcode Decoder
- 43 programmable keys
- OPOS and JavaPOS for Windows™ and Linux, support of Client-Server architectures
- Efficient configuration with professional 'Cherry-Tools' software
- Two USB downstream ports at the right rear

Agency Approvals

- GS (G81-8000) resp. VDE/ÜG (G81-7000), CE, FCC, cURus, C-Tick, VCCI, BSMI, GOST-R, WHQL, Designed for Windows™ XP

System Requirements

- USB plug and supporting operating system
- Operating System depending on software to be used

Delivery Volume

- 1 MultiBoard Keyboard
- 1 Printed Manual
- 1 CD-ROM

Magnetic Stripe Reader

- Optional 2- or 3-track reader
- Freely-programmable Header and Terminator per track
- Adjustable transmission of start/stop characters (sentinels)
- Enhanced card processing security with selection of non-keyboard hex codes
- Audible indication of Magnetic Stripe Card good or bad read; adjustable duration
- Free parsing and configuration of Magnetic Stripe data stream
- Free selectable output order of the tracks

Professional Software

- Programming of software macros with powerful configuration software 'Cherry Tools'
- Plug 'n' Play configuration
- UPOS support for Windows™ and Linux; Support of Client-Server architectures
- Supports Windows™ system functionalities
- Easy configuration file transfer with Windows™ Explorer
- Remote Network and immediate installation with 'Cherry Tools Runtime' version

Guarantee period

- 2 years

Software

- Cherry Tools
- Cherry Tools Runtime Edition
- Magnetic Stripe Reader Support for Linux
- OPOS Support
- JavaPOS Support for Windows™ & Linux

Technical Data

- Interface:
USB 2.0 (1.1 compatible)
- Downstream Ports
Two USB downstream ports at the right rear
USB 2.0, full speed
- Cable Length:
approx. 1.75 m
- Magnetic Stripe Reader:
Standards: ISO 7811/-12, AAAMVA, JIS 1/2
Gemini (others on request)
Reading Cycles: up to 1 Mio. Card Swipes
Swipe speed: 3 - 125 inch/s at 75 Bit/inch
3 - 50 inch/s at 210 Bit/inch
- Number of Keys:
104 = international layout with Windows™ keys
105 = European layout with Windows™ keys
- Weight:
G81-7000:
max. 1650 g (without packaging)
max. 2000 g (incl. packaging)
G81-8000:
max. 1950 g (without packaging)
max. 2300 g (incl. packaging)
- Dimensions:
G81-7000:
approx. 405x220x64 mm (keyboard)
approx. 455x277x72 mm (packaging)
G81-8000:
approx. 470x220x64 mm (keyboard)
approx. 521x277x72 mm (packaging)
- Operating life time of individual keys:
> 50 Mio operations
- Current Input:
max. 400 mA
- Current Output:
max. 100 mA per downstream port
- Reliability:
MCBF > 10⁹ operations
MTBF > 100.000 hours
- Storage Temperature:
-20°C to 60°C
- Operating Temperature:
0°C to 50°C
- Packaging Unit:
G81-7000: 34 keyboards per master carton
G81-8000: 31 keyboards per master carton
2 master cartons per pallet

Order Description

<i>Order Number</i>	<i>Magnetic Stripe Reader Tracks</i>	<i>Colour</i>
Compact Version		
G81-7000LUAxx-0	1+2+3	light grey
G81-7000LUAxx-2	1+2+3	black
G81-7000LUBxx-0	1+2	light grey
G81-7000LUBxx-2	1+2	black
Standard Version		
G81-8000LUAxx-0	1+2+3	light grey
G81-8000LUAxx-2	1+2+3	black
G81-8000LUBxx-0	1+2	light grey
G81-8000LUBxx-2	1+2	black

The xx in the Order Number defines the country version as follows:

European layout:

BE Belgium
 CH Switzerland
 DE Germany
 DK Denmark
 ES Spain
 FR France
 GB English (UK)
 IT Italy
 NO Norway
 PO Portugal
 SF Sweden/ Finland

International layout:

EU US English with €-Symbol
 US English (US)

(Other country versions upon request.)

Cherry GmbH
 Cherrystraße
 91275 Auerbach/Opf.
 Germany

Phone: +49 9643 18 0
 Internet: www.cherry.de

Sales: +49 1805 243779 (+49 1805 CHERRY)
 E-Mail: sales@cherry.de
 Fax: +49 9643 18 1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 05.08.2008_V11

