

USB-Hub keyboard

G83-6504



Facts & Features

- Integrated USB hub with four downstream ports for easy and comfortable connection of USB devices (plug and play)
- Space-saving, compact design
- Recyclable, with long span
- Uniform switching characteristics
- Comfortable actuation with soft-tactile point
- Abrasion-proof inscription of key caps
- PC- and MAC compatible due to USB interface

Delivery volume

- 1 USB-Hub keyboard
- 1 printed manual

Approvals

- FCC, cURus, GS, CE, c-tick, GOST-R, VCCI
- Microsoft Windows TMXP

System requirements

- USB interface

Technical data

- Number of buttons:
104 = international layout with Windows TM keys
105 = european layout with Windows TM keys
- Weight:
approx. 1140 g (keyboard)
approx. 1350 g (with packaging)
- Dimensions:
approx. 458 x 195 x 42 mm (keyboard)
approx. 493 x 255 x 52 mm (packaging)
- Cable length:
approx. 1.75 m
- Storage temperature:
-20 °C to 60 °C
- Operating temperature:
0 °C to 50 °C
- Operating life of individual keys:
> 20 million operations
- Interface:
USB
- Current consumption:
max. 500 mA
- Current output:
max. 100 mA per downstream port
- Transmission speed:
max. 12 Mbit/s
- Packaging unit:
51 keyboards per master carton
2 master cartons per pallet
- Guarantee period:
2 years

Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Number of buttons</i>	<i>Country version</i>	<i>EAN-Code</i>
G83-6504LADBE-0	light grey	105	Belgium	4025112052552
G83-6504LADCH-0	light grey	105	Switzerland	4025112048753
G83-6504LADCH-2	black	105	Switzerland	4025112054884
G83-6504LADDE-0	light grey	105	Germany	4025112010743
G83-6504LADDE-2	black	105	Germany	4025112055898
G83-6504LADDK-0	light grey	105	Denmark	4025112010750
G83-6504LADDK-2	black	105	Denmark	4025112055812
G83-6504LADES-0	light grey	105	Spain	4025112014352
G83-6504LADES-2	black	105	Spain	4025112055836
G83-6504LADEU-0	light grey	104	US-English with €	4025112035791
G83-6504LADFR-0	light grey	105	France	4025112010767
G83-6504LADFR-2	black	105	France	4025112055782
G83-6504LADGB-0	light grey	105	UK-English	4025112010828
G83-6504LADGB-2	black	105	UK-English	4025112052880
G83-6504LADIT-2	black	105	Italy	4025112055829
G83-6504LADNO-0	light grey	105	Norway	4025112010774
G83-6504LADNO-2	black	105	Norway	4025112055799
G83-6504LADRG-0	light grey	104	US-English / Cyrillic	4025112005930
G83-6504LADSF-0	light grey	105	Sweden / Finland	4025112010781
G83-6504LADSF-2	black	105	Sweden / Finland	4025112055843
G83-6504LADSK-0	light grey	105	Slovakia	4025112045752
G83-6504LADSL-0	light grey	105	Slovenia	4025112028441
G83-6504LADSL-2	black	105	Slovenia	4025112055805
G83-6504LADTS-0	light grey	105	Czech Republic	4025112022920
G83-6504LADUS-2	black	104	US-English	4025112055461

Cherry GmbH
Cherrystraße
91275 Auerbach/Opf.
Germany

Phone: +49 9643 18-0
Internet: www.cherry.de
www.cherrycorp.com

Sales: +49 1805 243779 (01805-Cherry)
E-Mail: sales@cherry.de
Fax: +49 9643 18-1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 30.07.2008_V02

