


4

3


2

1


UNIT: mm



PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑨ PE BAG		1/10	CLEAR SIZE: 280*330*0.05mm	PRINT BLACK "MADE IN CHINA" + "10PCS"
⑧ PE BAG		1	CLEAR SIZE: 130*230*0.05mm	PRINT BLACK "MADE IN CHINA"
⑦ TIE		2	WHITE L=100mm	
⑥ IN JACKET		3g	CLEAR LDPE (MOULD NO: NM-027)	
⑤ OUT JACKET		7g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-83)	
④ OUT JACKET		6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-40)	
③ CABLE		1	BEIGE (IV-29#) USB1.1 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=1780 ± 10mm	
② CONN		1	USB A FEMALE SHELL: NICKEL, PIN G/F SHORT TYPE, INSULATOR COLOR: WHITE	
① CONN		1set	USB A MALE SHELL: NICKEL, PIN G/F 3PCS TYPE, INSULATOR COLOR: WHITE	
NO.		NAME	SPECIFICATION	

CNC Tech, LLC		Industrial Cable and Connector Technology		
DRAWN	Andy	DRAWING NO		
CHECKED		CUSTOMER		
APPROVAL		ITEM NO.	101-1010-BE-00180	
DECIDED		DATE	2013-8-23	
VERSIONS/EDITION	A/0	PROJECTION		

A

A

B

B

C

C

D

D