



UNIT: mm




CABLE BLACK PRINT
USB CABLE E189529  AWM 2725 28AWG/1PR AND
24AWG/2C 80°C 30V VW-1

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V



1PCS/PE BAG

⑥	PE BAG	1/10	CLEAR SIZE: 230*300*0.05mm	PRINT BLACK	MADE IN CHINA	"10PCS"
⑤	PE BAG	1	CLEAR SIZE: 100*200*0.05mm	PRINT BLACK	MADE IN CHINA	"1PC"
④	TIE	2	WHITE L=80mm			
③	OUT JACKET	12g	BEIGE (1V-29#)	PVC-40P (MOULD NO: WM-40)		
②	CABLE	1	BEIGE (1V-29#)	USB1.1 UL2725 28#/1P-24#/2C+AEB OD: 4.7mm L=1000+10/-0MM		
①	CONN	2set	USB A MALE SHELL-NICKEL	PIN G/F INSULATION COLOR WHITE	3PCS TYPE	
NO.	NAME	Q'TY	SPECIFICATION			

Cnc Tech, LLC						
Industrial Cable and Connector Technology						
DRAWED	Andy	DRAWING NO				
CHECKED		CUSTOMER				
APPROVAL		ITEM NO.				
DECIDED		DATE				
VERSIONS/EDITION	A/0	PROJECTION				

2013-8-23

