




UNIT:mm



CABLE WHITE PRINT
USB CABLE E189529 **RU** AWG 27/25 VW-1 30V 80°C 28AWG/1PR AND 28AWG/2C

PIN ASSIGNMENT:



Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:2 0hm(max)
3.Insulation resistance:10Mohm(min)
4.dielectric test:DC 300V

CnC Tech, LLC			
Industrial Cable and Connector Technology			
⑧	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS".
⑦	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC".
⑥	TIE	1	BLACK L=100mm
⑤	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:WM-40)
④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:WM-88)
③	CABLE	1	BLACK USB1.1 UL2725 28#/1P+28#/2C+AEB OD:3.8mm L=2000±10
②	CONN	1set	USB A MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK
NO.	NAME	Q' TY	SPECIFICATION
VERSIONS/EDITION		A/0	PROJECTION
			