




UNIT:mm



CABLE WHITE PRINT
USB CABLE E189529 **RU** AWG 2725 VW-1 30V 80°C 28AWG/1PR AND 28AWG/2C

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V

CnC Tech, LLC			
Industrial Cable and Connector Technology			
⑧ PE BAG		1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+ "10PCS".
⑦ PE BAG		1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+ "1PC".
⑥ TIE		1	BLACK L=120mm
⑤ OUT JACKET		6g	BLACK PVC-40P (MOULD NO: WM-40)
④ OUT JACKET		6g	BLACK PVC-40P (MOULD NO: WM-88)
③ CABLE		1	BLACK USB1.1 UL2725 28#/1P+28#/2C+AEB OD: 3.8mm L=3000±10
② CONN		1set	USB A MALE SHELL: NICKEL PIN: G/F 4PCS TYPE INSULATOR COLOR: WHITE
① CONN		1set	USB MINI 5P MALE SHELL: NICKEL PIN: G/F 3PCS INSULATOR COLOR: BLACK
No. NAME		Q' TY	SPECIFICATION
VERSIONS/EDITION		A/0	PROJECTION
			

4

3

2

1