




UNIT: mm



Electrical test:
1. 100% short open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V



PIN ASSIGNMENT:



⑥	PE BAG	1/10	CLEAR SIZE: 230*300*0.05mm PRINT BLACK"MADE IN CHINA"+ "10PCS".
⑤	PE BAG	1	CLEAR SIZE: 100*200*0.05mm PRINT BLACK"MADE IN CHINA"+ "1PC".
④	TIE	2	BLACK L=80mm
③	OUT JACKET	12g	BLACK PVC-40P (MOULD NO: WM-40)
②	CABLE	1	BLACK USB2.0 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=1000±10MM
①	CONN	2set	USB A MALE SHELL-NICKEL PIN G/F INSULATION COLOR WHITE 3PCS TYPE
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1020-BL-00100
DECIDED		DATE	2013-08-23
VERSIONS/EDITION	A/0	PROJECTION	