



UNIT: mm




PIN ASSIGNMENT:



Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: 2 Ohm(max)
- 3. Insulation resistance: 10Mohm(min)
- 4. dielectric test: DC 300V



1PCS/PE BAG

⑧	PE BAG	1/10	CLEAR SIZE: 230*300*0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS"
⑦	PE BAG	1	CLEAR SIZE: 100*200*0.05mm PRINT BLACK "MADE IN CHINA" + "1PC"
⑥	TIE	2	WHITE L=80mm
⑤	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-65)
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-40)
③	CABLE	1	BEIGE (IV-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=1000+10/-0mm
②	CONN	1set	USB2.0 B MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	1set	USB2.0 A MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
NO.	NAME	Q' TY	SPECIFICATION

Cnc Tech, LLC

Industrial Cable and Connector Technology

DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1030-BE-00100
DECIDED		DATE	2012-02-14
VERSIONS/EDITION	A/0	PROJECTION	

