



UNIT: mm




PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V

IPC/PE BAG



⑧	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK "MADE IN CHINA"+ "10PCS" 及印生产周期, 有透气孔.
⑦	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK "MADE IN CHINA" 及印生产周期, 有透气孔.
⑥	TIE	2	BLACK L=100mm
⑤	OUT JACKET	6g	BLACK PVC-45P (MOULD NO: WM-65)
④	OUT JACKET	6g	BLACK PVC-45P (MOULD NO: WM-40)
③	CABLE	1	BLACK USB2.0 UI 2725 28#/1P+24#/2C+AEB OD: 4.7mm L=3000±20mm
②	CONN	1set	USB2.0 B MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	1set	USB2.0 A MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
NO.	NAME	Q' TY	SPECIFICATION

Cnc Tech, LLC

Industrial Cable and Connector Technology

DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1030-BL-00300
DECIDED		DATE	2012-02-14
VERSIONS/EDITION	A/0	PROJECTION	