




UNIT:mm



CABLE BLACK PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+28AWG/2C
E189529 AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:2 0m(max)
3.Insulation resistance:10Mohm(min)
4.dielectric test:DC 300V

⑧	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS".	CnC Tech, LLC Industrial Cable and Connector Technology DRAWN ZHONGHS CHECKED APPROVAL DECIDED VERSIONS/EDITION A/0 PROJECTION 102-1031-GR-00200 2012-02-15			
⑦	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"				
⑥	TIE	2	WHITE L=100mm				
⑤	OUT JACKET	6g	GREY(A-112#) PVC-40P (MOULD NO:WM-40)				
④	OUT JACKET	6g	GREY(A-112#) PVC-40P (MOULD NO:WM-88)				
③	CABLE	1	GREY(A-112#) USB2.0 UL2725 28#/1P+28#/2C+AEB OD:3.8mm L=2000±15				
②	CONN	1set	USB2.0 A MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE				
①	CONN	1set	USB2.0 MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK				
NO	NAME	Q'TY	SPECIFICATION				

4

3

2

1