



UNIT:mm




CABLE BLACK PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+28AWG/2C
E189529 AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:




Electrical test:

- 1.100% short,open,miswire test
- 2.Conduct resistance:2 Ohm(max)
- 3.Insulation resistance:10Mohm(min)
- 4.dielectric test:DC 300V



NOTE:

1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:



2.外箱两个侧边ITEM NO后面各贴一个35*22mm ROHS标签。

⑦	PE BAG	1/5	CLEAR SIZE: 330*380*0.05mm PRINT BLACK"MADE IN CHINA"+5PCS"及印生产日期,有透气孔.
⑥	PE BAG	1	CLEAR SIZE: 210*250*0.05mm PRINT BLACK"MADE IN CHINA"+1PC"及印生产日期,有透气孔.
⑤	TIE	1	WHITE L=80mm
④	OUT JACKET	12g	GRAY(A-112#) PVC-50P (MOULD NO:WM-40 & WM-88)
③	CABLE	1	GRAY(A-112#) USB2.0 UL2725 28#/1P+28#/2C+AEB OD:3.8mm L=5000±20mm
②	CONN	1set	USB2.0 刺破式 ATYPE MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 刺破式 MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK
NO.	NAME	Q'TY	SPECIFICATION

VEGA TECHNOLOGIES INDUSTRIAL (AUSTRIA) CO.

DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1031-GR-00500
DECIDED		DATE	2012-02-15
VERSIONS/EDITION	A/0	PROJECTION	☉