




UNIT:mm



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑥	TIE	1	BLACK L=60mm
⑤	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"及印生产周期, 有透气孔.
④	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"及印生产周期, 有透气孔.
③	OUT JACKET	12g	BLACK PVC-40P (MOULD NO:WM-173)
②	CABLE	1	USB2.0 UL2725 [28AWG(7/0.12TC+AL)*1P+28AWG(7/0.12TC)*2C]+AEB(48B TC)
①	CONN	2	MICRO USB 5P A/M SOLDER TYPE SHELL:NICKEL PIN:G/F INSULATOR COLOR:BLACK
NO.	NAME	Q'TY	SPECIFICATION

Cnc Tech, LLC			
Industrial Cable and Connector Technology			
DRAWED	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1061-BL-00050
DECIDED		DATE	2012-02-16
VERSIONS/EDITION	A/0	PROJECTION	☉