

CABLE TIES

770-17XX-XX

BASIC PART NO. COLOR

VELCRO™ CABLE TIES

FEATURES

- REUSEABLE APPLICATION
- CUT & TRIM AS NEEDED

SPECIFICATION

Material:

LOW DENSITY POLYETHYLENE HOOK,
NYLON KNIT LOOP

PART NUMBER	FIG.	WIDTH	LENGTH OF ROLL
770-1740-XX	1	.75	5 YARDS
770-1741-XX	1	1	5 YARDS


COLOR CHART

BLK	RED	ORN	YEL	GRN	BLU
10	12	13	14	15	16


PART NUMBER	FIG.	A	L
770-1742-XX	2	1/2	6
770-1743-XX	2	1/2	8
770-1744-XX	2	1/2	11
770-1745-XX	2	3/4	15
770-1746-XX	2	3/4	24

COLOR CHART

BLK	RED	ORN	YEL	GRN	BLU
10	12	13	14	15	16



MIL-SPEC. CABLE CLAMPS AND TIES



SELF-LOCKING CABLE TIES MEETS APPLICABLE MIL SPECS

Double Pawled Head.

Double sided serration with positive locking.

White Nylon- Flexible & Conformable- Flame Retardant- Fungus Inert-
Resistant to Solvents, Alkalines and Grease. Operating temperature ranges
from 40°F to 185°F.

Various sizes, heavy duty- screw mounting types.

Self adhesive mounting plate available for some ties.

REGULAR (FIG. A)

Concord Part No.	Tensile Strength	M.S.No	Bundle Dia. Min.- Max.	Length Ref.	Width	Thick
770-1751	18	3367-4	1/16 - 5/8	3-3/4	.100	.053
770-1752	30	3367-5	1/16 - 1-1/4	5-13/16	.140	.053
770-1753	50	3367-1	1/16 - 1-3/4	7-15/16	.187	.053
770-1754	50	3367-7	1/16 - 3	12-1/16	.187	.053
770-1755	50	3367-2	1/16 - 4	15-1/16	.187	.053
770-1756	120	3367-3	3/16 - 4	15-1/16	.298	.080

SCREW MOUNTING (FIG. B)

Concord Part No.	Tensile Strength	Bundle Dia. Min.- Max.	Length	Width	Thick	Stud
770-1761	50	1/16 - 1-3/4	8-7/16	.187	.053	10
770-1762	50	1/16 - 4	15-9/16	.187	.053	10
770-1763	120	3/16 - 4	15-21/32	.298	.080	1/4


DOUBLE LOOP (FIG. C)

Double Loop to permit Double Looping, saving time and cost of additional ties.

770-1757	50	1/16 - 4	15-7/32	.187	.080	-
----------	----	----------	---------	------	------	---

MOUNTING PLATE PART NO: 770-1760

Self Adhesive - 1"x 1"




NYLON WIRE MARKER PLATES

Made of Nylon, attaches to wire harness with
any type of wire tie or lacing cord. Write in iden-
tification.
Reusable



PART NO.	SIZE
770-1770	3/4X1-1/2
770-1772	3/4X2

CABLE TIES NYLON LOCKING CLAMP CLAMP PART NO.: 770-1701



Ratchet design makes for positive holding. Accommodates cables from 1/8" to 1-3/4"
Just slip clamp around cable, insert tongue and pull tight

TWIST LOCK CABLE TIES

Cost saving white Nylon re-usable ties.


Twists to lock wire, twists to unlock

Part No. For Wire Dia.


770-1796	.200-.300
770-6731	.300-.400
770-1707	.400-.500
770-1708	.700-.800



BEADED WIRE TIES PART NUMBER: 770-1765



NYLON ADJUSTABLE CABLE TIE PART NUMBER: 770-1766



FOR ADDITIONAL SIZES AND MATERIAL, CONTACT FACTORY

CONCORD®