



- Notes:**
- Material and Finish:
 - Coupler Ring: Zinc Die-Cast, Nickel Plated
 - Plug Housing: Zinc Die-Cast, Nickel Plated
 - Cable Gland: Brass, Nickel Plated
 - Cable Gland Rubber Ring: NBR, Color: Black
 - Cable Fitting: PA (Black), UL94 V-0
 - Interfacial Seal: Silicone, Color: White
 - Protective Cap: Polyester (Black); UL94 V-0
 - Tether: Polycarbonate (Black)
 - Duplex LC Connector
 - Housing: PEI, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green**
 - Inner Sub Assembly: Zirconia, Metal and PTFE
 - Crimp Barrel: Brass, Nickel Plated
 - Ferrule: Brass, Nickel Plated
 - Dust Cap: PC, Color: White
 - Duplex LC Clip: PC, Color: Black
 - Operating Temperature: -40°C to +85°C
 - IP67 rated when covered or fully mated with the appropriate mating connector
 - Accepts 4.5mm to 8.0mm outside diameter fiber optic cable

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Nickel Plated Die-Cast Duplex LC Single Mode Plug Kit + Plastic Plug Cover Assembly	17-300410
Nickel Plated Die-Cast Duplex LC Multi Mode Plug Kit + Plastic Plug Cover Assembly	17-300420
Nickel Plated Die-Cast Duplex LC APC Single Mode Plug Kit + Plastic Plug Cover Assembly	17-300430

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.30 1 PLC ±0.20 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±1°		Scale:	Dim. in mm
	Name	Title	Approval Date			Material: See Notes	
	2011	Date	Name			Title: IP67 Industrial Duplex LC Plug + Protective Cover Assembly Kit	
	Draw.	Nov. 09	Vincent Ke			Nickel Plated Zinc Die-Cast Version	
Appd.	Nov. 09	J. Chaudry	Drawing No.: 17K1A303		DIN A3		
Rev.	Changes	Date	Name	Part No.: SEE PART NUMBER TABLE		Sheet 1/1	

