




Cirrus 80			
Nominal Power Output at 10°C		300/600W	450/800W
Typical max	at 230 AC, amps	10	11
	inrush current at 115 AC, amps	15	14
Fan volumetric flow, approximate, m3/hr		35	35
Fan lifetime at 40°C L10, hours		52,500	52,500
Normal input voltage		115V or 230VAC	115V or 230VAC
Dimensions	- cross section mm	82 x 110	82 x 110
	- length mm	150	150
Weight (g)		785	785
Finger guards inlet and outlet		Y	Y

Options
Filter Assembly*
Fixing - 35mm DIN clip

* Typical power reduction of 10% when 30PPI filter fitted
Data is given for illustration purposes only and does not release the customer from independent application tests.
This information is subject to change without notice.