




NOTES:

1. ALL DIMENSIONS IN INCHES
2. MAT'L CRS TYPE SAE 1050
3. PLATING SPEC.:
HEAT TREAT TO RC 44-48
SULFAMATE NICKEL, DUCTILE
NICKEL PLATE .00015/.00025
COPPER STRIKE .00020/.00050
4. NO. OF TEETH 9 EQUALLY SPACED
5. MINIMUM PROJECTION OF ANY SINGLE
TOOTH SHALL BE .00015

TOOTH SHALL BE .00015							
D	REVISED & REDRAWN	9/28/98					
REV.	DESCRIPTION	DATE	CHKD				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							
				TOLERANCES			
				±0.4			
				±0.25			
				TITLE			
				LOCK WASHER HDW11 -1/4-40UNS			
SCALE		DATE		DR		REV	
4:1		8/25/95		MM		T100011	
				DWG		D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[HDW11](#)