





Dimensions: mm (In.)

SPECIFICATIONS	
Rated current:	10A
Insulation resistance:	100m Ω min. at 500V DC
Contact resistance:	5m Ω at 1A DC
Dielectric strength:	AC 1500V min. for 60 seconds
Body material:	P.V.C.
Wire:	18# AWG Wire
Terminal:	Crimp terminal
Lock:	Snap-lock type
Contact:	Brass, tin/nickel plated

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-EPD209F2](#)