



DIMENSIONS: mm (In.)

| SPECIFICATIONS | |
|--|--------------------------|
| Rated Current: | 30 A |
| Insulation resistance @ 500V DC: | 100MΩ Min. |
| Contact resistance: | 5 mΩ @ 1A DC |
| Dielectric strength for 60 seconds: | AC 1500V Min. |
| Body material: | Flame retardant nylon 66 |

- Terminal type
- Interlock for multiple mounting
- Contact: Brass, tin/nickel plated
- To install fuses with "loop" type wires, simply cut loop in two to form separate wires of desired length.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-EPD211TN](#)