


**Series EM3583**

**EuroMag Terminal Blocks**

IDC Pluggable Block

(Mates with EM3593 Series); 3.81 Centers



EM358307

**SPECIFICATIONS**

**Ratings:** 10A, 160V

**Center Spacing:** 0.15" (3.81mm)

**Wire Range:** #18-20 AWG

**Housing Material:** UL rated 94V0 Thermoplastic

**Contact Material:** Brass, Tin-Plated


**Operating Temperature:** 105°C (221°F) max., -49°C (-40°F) min.

**Construction:** Mold-to-length.

**Agency Information:** cULus File E62622; CE Certified

Poles	L1 (mm)	L2 (mm)	Poles	L1 (mm)	L2 (mm)
02	3.81	8.40	08	26.67	31.26
03	7.62	12.21	09	30.48	35.07
04	11.43	16.02	10	34.29	38.88
05	15.24	19.83	11	38.10	42.69
06	19.05	23.64	12	41.91	46.50
07	22.86	27.45			

**Dimensions - mm (in)**



**Part Numbering System**

Inches (Millimeters)

Series

**EM3583**

# of Positions

02 to 12

Mating Header: EM3593 pg. 81

Terminal Blocks:  
Single Row

EuroMag Series  
Plug & Header

Edge Connectors,  
One-Sided Boards

Compliance  
References