

Toggle Switches

RATINGS	CIRCUIT	TOGGLE POSITION			CATALOG NUMBER			
					TYPE OF TERMINATION			
		UP	CENTER	DOWN (keyway)	.187 Q.C.	SCREW	.250 Q.C.	SOLDER LUG

9100 SERIES TOGGLE

6A-125VAC 3A-250VAC	DPST	ON	NONE	OFF	9103A	9103B	9103C	9103D
	DPDT	ON	NONE	ON	9101A	9101B	9101C	9101D
		ON	OFF	ON	9102A	9102B	9102C	9102D

9000 SERIES TOGGLE

15A-125VAC 10A-250VAC	DPST	ON	NONE	OFF	9003A	9003B	9003C	9003D
	DPDT	ON	NONE	ON	9001A	9001B	9001C	9001D
		ON	OFF	ON	9002A	9002B	9002C	9002D

9200 SERIES TOGGLE

20A-125VAC 10A-250VAC ¾ HP, 125-250VAC	DPST	ON	NONE	OFF	9203A	9203B	9203C	9203D
	DPDT	ON	NONE	ON	9201A	9201B	9201C	9201D
		ON	OFF	ON	9202A	9202B	9202C	9202D

For .687 Toggle And .468 Bushing Length Add 100 To Part Number Specified
For Dust And Moisture Resistant Seal Add "S" To Part Number Specified

SPECIFICATIONS

Agency Listings



CSA Certified

Contact Mechanism

Slow-Make/Slow-Break Butt Contact

Contact Material

9100 Series:

Stationary - Copper Alloy/Silver Plated

Movable - Copper Alloy

9000 And 9200 Series:

Stationary (Center) - Copper Alloy/Silver Plated

Stationary (End) - Silver Cadmium Oxide Composite

Movable-Silver Cadmium Oxide Composite

Dielectric Strength

1000 Volts RMS Minimum

Mounting Means

15/32" Diameter Threaded Bushing

Keyway .078-.083 Wide X .037-.043 Deep

Standard Hardware Supplied —

One Hex Nut Assembled And

One Hex Nut Unassembled.

