

5

4

3

2

1

D



Description: CAT5E molded & booted patch cable
Part No: 73-779X-XXX
Application: Patch cable
Crimp Tool: N/A
Impedance: N/A
Frequency Range: N/A
Material: Plug RJ-45, Gold plated on contacts
Hood PVC
Cable UTP, 24 AWG, 4 twisted pairs, stranded bare copper, UL ETL EIA/TIA-568B verified category 5e

RoHS Compliance: Yes

Technical Detail: N/A

C

B

PIN ASSIGNMENT	
RJ-45 PLUG	RJ-45 PLUG
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8

X=COLOR
0-GRAY
1-BLACK
2-BLUE
3-GREEN
4-RED
5-YELLOW
6-WHITE
7-ORANGE
8-PINK
9-PURPLE

TABLE 1

PART NUMBER	LENGTH (FEET)	DESCRIPTION
73-779X-1	1	CAT5E MOLDED & BOOTED PATCH CABLE, 1FT
73-779X-1.5	1.5	CAT5E MOLDED & BOOTED PATCH CABLE, 1.5FT
73-779X-3	3	CAT5E MOLDED & BOOTED PATCH CABLE, 3FT
73-779X-5	5	CAT5E MOLDED & BOOTED PATCH CABLE, 5FT
73-779X-7	7	CAT5E MOLDED & BOOTED PATCH CABLE, 7FT
73-779X-10	10	CAT5E MOLDED & BOOTED PATCH CABLE, 10FT
73-779X-14	14	CAT5E MOLDED & BOOTED PATCH CABLE, 14FT
73-779X-25	25	CAT5E MOLDED & BOOTED PATCH CABLE, 25FT
73-779X-50	50	CAT5E MOLDED & BOOTED PATCH CABLE, 50FT
73-779X-100	100	CAT5E MOLDED & BOOTED PATCH CABLE, 100FT

DRAWING NO.
73-779X-XXX-CUST

REVISIONS

01

OFFICIAL RELEASE

03-28-11

J

J

J

D


2011.04.01
03/28/11

D

C

C

B



CUSTOMER COPY

A

DIM OUTLINE

受控 CONTROLLED DOCUMENT					
编号 P/N	73-779X-XXX-CUST	版本 Rev	01	日期 Rel'd Date	Jul11,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		JEAN.JIN	03-28-11
X		CHECKED BY	DATE
X.X		JEAN.JIN	03-28-11
X.XX		APPROVED BY	DATE
X.XX		DONALD	03-28-11
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.



Connectivity
Solutions

TITLE
CAT5E MOLDED & BOOTED PATCH CABLE

SHEET
1 OF 1

DRAWING NO.
73-779X-XXX-CUST

SIZE
A

A

5

4

3

2

1