



| A           |             | B            |            | C            |            | D |  |
|-------------|-------------|--------------|------------|--------------|------------|---|--|
| PART NUMBER | "ID"        | "H"          | "P"        | "OD"         | "T"        |   |  |
| HG-2        | 3.2 [.126]  | 4.8 [.190]   | 1.6 [.063] | 8.0 [.315]   | 6.4 [.252] |   |  |
| HG-2.5      | 4.0 [.148]  | 6.4 [.252]   | 1.6 [.063] | 9.5 [.374]   | 6.3 [.248] |   |  |
| HG-3        | 4.8 [.188]  | 7.7 [.305]   | 0.8 [.032] | 10.9 [.430]  | 4.8 [.188] |   |  |
| HG-3.5      | 5.5 [.217]  | 8.0 [.315]   | 1.6 [.063] | 10.9 [.430]  | 5.5 [.217] |   |  |
| HG-4        | 6.4 [.252]  | 9.5 [.374]   | 2.4 [.095] | 14.2 [.559]  | 7.0 [.276] |   |  |
| HG-5        | 8.0 [.313]  | 10.9 [.430]  | 1.6 [.063] | 14.3 [.562]  | 4.8 [.188] |   |  |
| HG-6        | 9.5 [.374]  | 12.5 [.492]  | 1.6 [.063] | 17.0 [.669]  | 7.0 [.276] |   |  |
| HG-8        | 12.6 [.495] | 16.8 [.660]  | 1.6 [.063] | 21.5 [.846]  | 6.4 [.250] |   |  |
| HG-9        | 14.2 [.558] | 17.1 [.675]  | 1.6 [.063] | 22.2 [.875]  | 4.8 [.188] |   |  |
| HG-10       | 15.5 [.610] | 18.8 [.742]  | 1.6 [.063] | 22.2 [.875]  | 5.6 [.219] |   |  |
| HG-11       | 17.1 [.672] | 18.7 [.735]  | 1.6 [.063] | 23.7 [.933]  | 4.8 [.188] |   |  |
| HG-12       | 18.6 [.734] | 24.8 [.976]  | 1.6 [.063] | 31.3 [1.234] | 8.0 [.313] |   |  |
| HG-14       | 21.8 [.860] | 25.1 [.990]  | 1.6 [.063] | 30.2 [1.188] | 8.0 [.313] |   |  |
| HG-16       | 24.6 [.970] | 31.5 [1.240] | 1.6 [.063] | 38.1 [1.500] | 8.0 [.313] |   |  |
| HG-17       | 8.0 [.315]  | 11.0 [.433]  | 2.0 [.079] | 16.0 [.630]  | 7.0 [.276] |   |  |
| HG-18       | 12.7 [.500] | 19.0 [.748]  | 2.4 [.095] | 24.0 [.945]  | 7.1 [.280] |   |  |

| REV. | MODIFICATION. | DATE     | DRN |
|------|---------------|----------|-----|
| A    | NEW DRAWING   | 22/12/95 | RMB |
| 02   | ECN2005-043   | 06/04/05 | OW  |
| 03   | ECN2006-031   | 18/01/06 | OW  |
| 04   | ECN2006-092   | 06/06/06 | TC  |
| 05   | ECN2006-217   | 04/09/06 | TC  |
| 06   | ECN2007-013   | 15/01/07 | SF  |
| 07   | ECN2007-018   | 22/01/07 | SF  |
| 08   | ECN2007-055   | 28/03/07 | SF  |
| 09   | ECN2007-063   | 16/04/07 | SF  |
| 10   | CO2010068     | 26/02/08 | SF  |
| 11   | CO2010071     | 27/02/08 | SF  |
| 12   | CO2010653     | 13/05/09 | SF  |



NOTES  
1a) METRIC PRIMARY UNITS:mm  
1b) IMPERIAL SECONDARY UNITS: [inches]  
2) ALL RMS-262 PARTS (UL94-HB) ARE AVAILABLE  
IN RMS-263 (UL94-V0) BY SPECIAL ORDER  
3) PART AVAILABLE IN GREY BY SPECIAL ORDER.  
ADD GY TO PART NUMBER AS FOLLOWS: HG-2.5GY.



|                                                                                                                                                                                |  |                                                                                                 |  |                       |  |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------|--|-----------------------|--|
| INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT. |  |                                                                                                 |  |                       |  |
|                                                                                                                                                                                |  | GENERAL TOLERANCE:<br>FOR REFERENCE ONLY ±0.50 [0.02]<br>UNLESS OTHERWISE STATED<br>ANGULAR ±1° |  |                       |  |
| MATERIAL:<br>RMS-262 TPE (see notes)                                                                                                                                           |  | THIRD ANGLE<br>                                                                                 |  |                       |  |
| DESCRIPTION:<br>HG-X                                                                                                                                                           |  | COLOUR:<br>BLACK                                                                                |  |                       |  |
| DRG No:<br>760-0001                                                                                                                                                            |  | NPR No:<br>N/A                                                                                  |  | PART No:<br>SEE TABLE |  |
| DRN<br>OW                                                                                                                                                                      |  | DATE<br>06/04/05                                                                                |  | SHEET SIZE<br>A4      |  |
| CHKD<br>NBr                                                                                                                                                                    |  | DATE<br>08/04/05                                                                                |  | SCALE<br>NTS          |  |
|                                                                                                                                                                                |  |                                                                                                 |  | SHEET No.<br>1 OF 1   |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[HG-16](#) [HG-10](#) [HG-11](#) [HG-12](#) [HG-14](#) [HG-17](#) [HG-18](#) [HG-2](#) [HG-2.5](#) [HG-3](#) [HG-4](#) [HG-5](#) [HG-6](#) [HG-8](#) [HG-9](#)