

FEX FEX 2819 13 T



Sample photo

Order symbol: FEX 2819 13 T
Product nbr: 4120801
Description: Enclosure, PC
Remarks: Ex e II, EN 60079; IK 4J

EAN:	6418074007902
El. number:	
Finland:	3424642
Denmark:	8212026353
Italy:	7801020
Sweden:	4120801
Norway:	

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	278	188	130
inch:	10.9	7.4	5.1

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035
Cover colour:	Clear transparent
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Silicone

Temperatures:

Short term:	-40 ... 120 °C
Continuous:	-10 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	14 ... 175 °F

Accessories:

EKHVT	Mounting plate
EKJVT	Mounting plate
EKMVT	Mounting plate
EKOVT	Mounting plate
EKPVT	Mounting plate
EKTVT	Mounting plate
EKUVT	Mounting plate
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail

Rating:

Ingress Protection (EN 60529): IP 54
Impact Resistance (EN 50014): 4J
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes

Certificates:

ATEX
EC Certificate of Conformity

SOLID 278x188x130-180

