

You are here: [Products](#) » [Connectors f.con](#) » [PCB connectors](#) » [Female headers](#) » [BLP 2 ...](#) » [BLP 2](#)

▶ Heatsinks f.cool

▶ Cases f.case

▼ Connectors f.con

▶ Sockets

▼ PCB connectors

■ Male headers

■ Female headers

■ Direct female connector

■ Jumpers

▶ IDC-connectors

▶ D-Sub connectors

■ Brackets for PC

▶ Optoelectronics

Female headers

BLP 2 26

High-precision female headers square 0,635 mm and pins up to 0,85 mm Ø; Press-fit mounting without soldering, resilient press-fit area.

add to request



Features Technical Drawing Accessories / related products Further Information

no. of contacts	26
contact sleeve	tin-plated
contact material	CuZn-alloy
contact spring	gold-plated
surface contact / contact sleeve	Ni+4...6µm Sn
inner contact spring material	CuBe-alloy
inner contact spring surface	
Typ Innenfeder	
plugability	
Einstecktiefe	
insertion / extraction force	
shock resistance	50 g
vibration resistance max.	15 g
volume resistivity	
capacity between two adjacent contacts	≤ 0,3 pF
nominal current	2 A
nominal voltage	
test voltage	1000 V
material isolation body	
temperature range	
class of flammibility	UL 94 V-0
insulation resistance	
version	female header
connection type	insertion
reflow solderable	yes