

Bus Drop Cable

60°C 600 Volt UL Listed

Product Construction:

Conductors:

- 14 through 6 AWG annealed stranded bare copper per ASTM B-8 or B-174 as applicable

Insulation:

- Premium-grade, color-coded Polyvinylchloride (PVC)
- Color code: black, white, red

Jacket:

- Polyvinylchloride (PVC) jacket, gray
- Temperature range: -20°C to +60°C

Jacket Marking:

- INDENT PRINT: (SIZE) BUS DROP 600V (UL)

Applications:

- As branches from busways per NEC
- Connection of stationary equipment to facilitate relocation of equipment

Features:

- Used in dry location
- One uninsulated ground conductor per interstice (3 ground conductors total)
- Resistant to oils, lubricants, water, acids, alkalis, ozone and abrasion

Industry Approvals:

- UL Listed
- RoHS Compliant

Packaging:

- 250' reel (76.2 m) as standard
- 500' (152.4 m) and 1000' (304.8 m) reels also available
- Other put-ups available on special order



BUS DROP CABLE— 600 VOLT — UL

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS [†]	APPROX. NET WEIGHT LBS/M ^(S)	STD. CTN.
				INCHES	mm	INCHES	mm			
03714	3	14	19	0.030	0.76	0.400	10.16	15	120	250'
03712	3	12	19	0.030	0.76	0.425	10.80	20	150	250'
03710	3	10	19	0.030	0.76	0.485	12.32	30	225	250'
03708	3	8	19	0.045	1.14	0.625	15.88	40	370	250'
03706	3	6	19	0.060	1.52	0.770	19.56	55	600	250'

[†] Ampacities based on NEC table 400.5(A).

^(S) Actual shipping weight may vary.