

Low-Voltage Sprinkler Wire

60°C 30 Volts UL



LOW-VOLTAGE SPRINKLER WIRE - 30 VOLT - UL

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FEET)	PACKAGE TYPE	POWER RATING ⁽¹⁾			PKG PER CTN.	APPROX. WEIGHT PER CTN. (LBS) ⁽²⁾
					VOLTS	AMPS	WATTS		
23824.60.01	4	18	100	Cuff	30	5.6	168	6	22
23804.18.01	4	18	500	Spool	30	5.6	168	1	18
23815.60.01	5	18	50	Cuff	30	5.6	168	6	13
23825.60.01	5	18	100	Cuff	30	5.6	168	6	27
23805.18.01	5	18	500	Spool	30	5.6	168	1	22
23817.60.01	7	18	50	Cuff	30	4.9	147	6	18
23827.60.01	7	18	100	Cuff	30	4.9	147	6	36
23807.18.01	7	18	500	Spool	30	4.9	147	1	31
23810.18.01	10	18	500	Reel	30	3.5	165	1	44

⁽¹⁾ Amps and watts are offered ONLY as a guide to the end user.

⁽²⁾ Actual shipping weight may vary.

Product Construction:

Conductor:

- 18 AWG fully annealed solid bare copper per ASTM B-3

Insulation:

- Premium-grade, color-coded PVC
- Premium-grade PE jacket, black
- Nylon rip cord to facilitate jacket removal
- Temperature range: -20°C to +60°C
- Color code: See chart below

Jacket Marking:

- CAROL (SIZE) 30V SPRINKLER SYSTEMS WIRE - DIRECT BURIAL E54567 (UL)

Applications:

- Low-voltage golf course satellite sprinkler control
- Residential sprinkler solenoid control

Industry Approvals:

- UL Listed under a UL Miscellaneous Wire file
- UL Listed for outdoors applications
- UL Listed for direct burial applications
- RoHS Compliant

Packaging:

- See tabular data above
- Other put-ups available on special order

COLOR CODE CHART

1	Black	4	Green	7	Blue	10	Purple
2	White	5	Orange	8	Brown		
3	Red	6	Yellow	9	Gray		

