


Blind Rivets Alu Standard

corresponding to DIN 7337

(Dome Head)

Rivet Body: Alu AlMg 3
Mandrel: Steel, zinc plated



	Rivet Body D ₁ x L mm	Grip Range mm	Part- No.	Quantity per Box	£ per 1000 pcs.	
2,4 Hole Ø: 2,5 mm	2,4 x 4	0,5 - 2,0	630 0014	A 1000	19.48	B
	2,4 x 6	2,0 - 4,0	630 0022	"	21.52	B
	2,4 x 8	4,0 - 6,0	630 0030	"	23.44	B
3 Hole Ø: 3,1 mm	3 x 4	0,5 - 1,5	630 0103	A 500	19.48	B
	3 x 5	1,5 - 2,5	630 0111	"	19.53	B
	3 x 6	2,5 - 3,5	630 0138	"	19.67	B
	3 x 7	3,5 - 4,5	630 0146	"	20.07	B
	3 x 8	4,5 - 5,5	630 0154	"	21.97	B
	3 x 10	5,5 - 7,0	630 0162	"	23.69	B
	3 x 12	7,0 - 9,0	630 0170	"	26.20	B
	3 x 14	9,0 - 11,0	630 0189	"	30.55	B
	3 x 16	11,0 - 13,0	630 0197	"	30.89	B
	3 x 18	13,0 - 15,0	630 0200	A 250	37.68	B
	3 x 20	15,0 - 17,0	630 0219	"	43.56	B
	3 x 25	17,0 - 22,0	630 0227	"	53.98	B
	3 x 30	22,0 - 26,0	630 0235	"	64.34	B
3,2 Hole Ø: 3,3 mm	3,2 x 4	0,5 - 1,5	630 0308	A 500	11.73	A
	3,2 x 6	1,5 - 3,5	630 0316	"	12.03	A
	3,2 x 8	3,5 - 5,5	630 0324	"	13.30	A
	3,2 x 10	5,5 - 7,0	630 0332	"	13.95	A
	3,2 x 12	7,0 - 9,0	630 0340	"	14.67	A
	3,2 x 14	9,0 - 11,0	630 0081	"	22.04	A
	3,2 x 16	11,0 - 13,0	630 0359	B 500	24.38	A
	3,2 x 18	13,0 - 15,0	630 0383	"	40.92	B
	3,2 x 20	15,0 - 17,0	630 0367	"	45.89	B
3,2 x 25	17,0 - 22,0	630 0375	"	55.70	B	

	Rivet Body D ₁ x L mm	Grip Range mm	Part- No.	Quantity per Box	£ per 1000 pcs.	
4 Hole Ø: 4,1 mm	4 x 5	0,5 - 1,5	630 0405	A 500	13.90	A
	4 x 6	1,5 - 3,0	630 0413	"	14.09	A
	4 x 7	3,0 - 4,0	630 0421	"	14.26	A
	4 x 8	4,0 - 5,0	630 0448	"	14.45	A
	4 x 10	5,0 - 6,5	630 0456	"	14.86	A
	4 x 12	6,5 - 8,5	630 0464	B 500	15.09	A
	4 x 14	8,5 - 10,5	630 0472	"	22.04	A
	4 x 16	10,5 - 12,5	630 0480	"	26.24	A
	4 x 18	12,5 - 14,5	630 0499	"	43.26	A
	4 x 20	14,5 - 16,5	630 0502	"	56.36	B
	4 x 25	16,5 - 21,5	630 0529	"	64.08	B
	4 x 30	21,5 - 26,0	630 0545	B 250	76.95	B
	4 x 35	26,0 - 30,0	630 0561	"	98.59	B
4,8 Hole Ø: 4,9 mm	4,8 x 6	0,5 - 3,0	630 0707	B 500	17.97	A
	4,8 x 8	3,0 - 4,5	630 0715	"	18.70	A
	4,8 x 10	4,5 - 6,0	630 0723	"	19.06	A
	4,8 x 12	6,0 - 8,0	630 0731	"	19.53	A
	4,8 x 14	8,0 - 10,0	630 0758	"	27.20	A
	4,8 x 16	10,0 - 12,0	630 0766	"	29.95	A
	4,8 x 18	12,0 - 14,0	630 0774	"	34.75	A
	4,8 x 20	14,0 - 16,0	630 0782	B 250	39.67	A
	4,8 x 25	16,0 - 21,0	630 0804	"	44.62	A
4,8 x 30	21,0 - 25,0	630 0820	A 100	52.10	A	

Ordering Example: Alu 4 x 20
Part-No. 630 0502

Rivet Ø mm	Shear strength		Tensile strength		Mandrel Ø mm	Max. head Ø mm
	N	(kp)	N	(kp)		
2,4	350	(35)	450	(46)	1,5	5,0
3	800	(81)	900	(92)	1,8	6,5
3,2	800	(81)	950	(97)	1,95	6,5
4 x 5-10	1.400	(143)	2.000	(204)	2,1	8,0
4 x 12-40 ■	850	(87)	1.000	(102)	2,1	8,0
4,8	2.000	(204)	2.700	(275)	2,7	9,5

■ Rivet Body: AlMgSi