

Series 80 Mighty Mouse

EMI Backshell Ordering Information

380MS137, 380MS135, 380MB137 and 380MA137



380MS135

EMI backshells feature an EMI ring for easy shield termination.

Straight Entry backshells are available with direct coupling or rotatable coupling.







45° and 90° adapters feature rotatable coupling nuts.

MATERIALS

Adapter, Clamp, Nut and Saddles	Aluminum Alloy 6061-T6 or 300 Series Stainless Steel
Hardware	300 Series Stainless Steel

HOW TO ORDER

Sample Part Number

380MS137	M	07	04-	6	N																																																																														
Part Number	Shell Material / Finish	Size Code	Cable Entry Code	Length	Clamp Style																																																																														
 380MS137 Straight Entry, Rotatable Coupling	C Aluminum / Black Anodize (Non-Conductive) RoHS Compliant M Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Cadmium with Olive Drab Chromate ZN Aluminum / Zinc-Nickel with Olive Drab Chromate ZNU Aluminum / Zinc-Nickel with Black Chromate MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant	<table><tr><th>Size Code</th><th>Thread Size</th></tr><tr><td>05</td><td>.2500-32</td></tr><tr><td>06</td><td>.3125-32</td></tr><tr><td>11</td><td>.3750-32</td></tr><tr><td>07</td><td>.4375-28</td></tr><tr><td>08</td><td>.5000-28</td></tr><tr><td>09</td><td>.5625-24</td></tr><tr><td>10</td><td>.6250-24</td></tr><tr><td>12</td><td>.6875-24</td></tr><tr><td>13</td><td>.7500-20</td></tr><tr><td>14</td><td>.9375-20</td></tr><tr><td>17</td><td>1.1875-18</td></tr></table>	Size Code	Thread Size	05	.2500-32	06	.3125-32	11	.3750-32	07	.4375-28	08	.5000-28	09	.5625-24	10	.6250-24	12	.6875-24	13	.7500-20	14	.9375-20	17	1.1875-18	<table><tr><th>Cable Entry Code</th><th>Saddle Clamp Dia. Fully Closed</th></tr><tr><td>01-</td><td>.11</td></tr><tr><td>02-</td><td>.17</td></tr><tr><td>03-</td><td>.23</td></tr><tr><td>04-</td><td>.30</td></tr><tr><td>05-</td><td>.36</td></tr><tr><td>06-</td><td>.42</td></tr><tr><td>07-</td><td>.48</td></tr><tr><td>08-</td><td>.55</td></tr><tr><td>09-</td><td>.61</td></tr></table>	Cable Entry Code	Saddle Clamp Dia. Fully Closed	01-	.11	02-	.17	03-	.23	04-	.30	05-	.36	06-	.42	07-	.48	08-	.55	09-	.61	Straight Entry 380MS Only <table><tr><th>Length Code</th><th>Length (Inches)</th></tr><tr><td>5</td><td>.625</td></tr><tr><td>6</td><td>.750</td></tr><tr><td>7</td><td>.875</td></tr><tr><td>8</td><td>1.000</td></tr><tr><td>9</td><td>1.125</td></tr><tr><td>10</td><td>1.250</td></tr><tr><td>11</td><td>1.375</td></tr><tr><td>12</td><td>1.500</td></tr><tr><td>13</td><td>1.625</td></tr><tr><td>14</td><td>1.750</td></tr><tr><td>15</td><td>1.875</td></tr><tr><td>16</td><td>2.000</td></tr><tr><td>17</td><td>2.125</td></tr><tr><td>18</td><td>2.250</td></tr><tr><td>19</td><td>2.375</td></tr><tr><td>20</td><td>2.500</td></tr></table> Specify length in increments of .125 inches (3.18 mm.)	Length Code	Length (Inches)	5	.625	6	.750	7	.875	8	1.000	9	1.125	10	1.250	11	1.375	12	1.500	13	1.625	14	1.750	15	1.875	16	2.000	17	2.125	18	2.250	19	2.375	20	2.500	 Omit for screw clamp with saddle bars  N Optional Compression Nut, Low Profile
Size Code	Thread Size																																																																																		
05	.2500-32																																																																																		
06	.3125-32																																																																																		
11	.3750-32																																																																																		
07	.4375-28																																																																																		
08	.5000-28																																																																																		
09	.5625-24																																																																																		
10	.6250-24																																																																																		
12	.6875-24																																																																																		
13	.7500-20																																																																																		
14	.9375-20																																																																																		
17	1.1875-18																																																																																		
Cable Entry Code	Saddle Clamp Dia. Fully Closed																																																																																		
01-	.11																																																																																		
02-	.17																																																																																		
03-	.23																																																																																		
04-	.30																																																																																		
05-	.36																																																																																		
06-	.42																																																																																		
07-	.48																																																																																		
08-	.55																																																																																		
09-	.61																																																																																		
Length Code	Length (Inches)																																																																																		
5	.625																																																																																		
6	.750																																																																																		
7	.875																																																																																		
8	1.000																																																																																		
9	1.125																																																																																		
10	1.250																																																																																		
11	1.375																																																																																		
12	1.500																																																																																		
13	1.625																																																																																		
14	1.750																																																																																		
15	1.875																																																																																		
16	2.000																																																																																		
17	2.125																																																																																		
18	2.250																																																																																		
19	2.375																																																																																		
20	2.500																																																																																		
 380MS135 Straight Entry, Direct Coupling																																																																																			
 380MB137 45° Entry																																																																																			
 380MA137 90° Entry																																																																																			

Dimensions in inches (millimeters) and are subject to change without notice.

CAGE Code 06324

Printed in U.S.A.

© 2011 Glenair, Inc.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912

www.glenair.com


L-26

E-Mail: sales@glenair.com


11 - JULY - 2013

Series 80 Mighty Mouse EMI Backshell Dimensions



380MS137, 380MS135, 380MB137 and 380MA137




STRAIGHT ENTRY
ROTATABLE COUPLING
380MS137




STRAIGHT ENTRY
DIRECT COUPLING
380MS135



CLAMP STYLE N
COMPRESSION NUT



45° ENTRY
ROTATABLE COUPLING
380MB137



90° ENTRY
ROTATABLE COUPLING
380MA137

DIMENSIONS

Size Code	A Thds.	B Max.		C Max.		Std. Length*	
		In.	mm.	In.	mm.	In.	mm.
05	.2500-32	.470	11.94	.350	8.89	.750	19.05
06	.3125-32	.530	13.46	.415	10.54	.750	19.05
11	.3750-32	.570	14.48	.465	11.68	.750	19.05
07	.4375-28	.637	16.18	.530	13.46	.750	19.05
08	.5000-28	.700	17.78	.595	15.11	.750	19.05
09	.5625-24	.758	19.25	.650	16.51	.750	19.05
10	.6250-24	.819	20.80	.715	18.16	.750	19.05
12	.6875-24	.896	22.76	.785	19.94	.880	22.35
13	.7500-20	.930	23.62	.830	21.08	.880	22.35
14	.9375-20	1.137	28.88	1.020	25.91	1.000	25.40
17	1.1875-18	1.387	35.23	1.280	32.51	1.130	28.70

*Choose standard length for best availability

DIMENSIONS

Cable Entry Code	D Max.		E Max.		F Max.		G Max.		H		Ø J Closed		Ø K		Ø L	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
01	.603	15.32	.581	14.76	.724	18.39	.702	17.83	.496	12.60	.110	2.79	.119	3.02	.398	10.11
02	.603	15.32	.581	14.76	.724	18.39	.702	17.83	.582	14.78	.170	4.32	.182	4.62	.460	11.68
03	.603	15.32	.581	14.76	.724	18.39	.702	17.83	.656	16.66	.230	5.84	.244	6.20	.523	13.28
04	.629	15.98	.607	15.42	.786	19.96	.764	19.41	.726	18.44	.300	7.62	.307	7.80	.585	14.86
05	.629	15.98	.607	15.42	.786	19.96	.764	19.41	.885	22.48	.360	9.14	.369	9.37	.647	16.43
06	.655	16.64	.633	16.00	.848	21.54	.826	20.98	.952	24.18	.420	10.67	.432	10.97	.710	18.03
07	.655	16.64	.633	16.00	.848	21.54	.826	20.98	1.018	25.86	.480	12.19	.494	12.55	.773	19.63
08	.707	17.96	.685	17.40	.911	23.14	.889	22.58	1.084	27.53	.550	13.97	.557	14.15	.835	21.21
09	.707	17.96	.685	17.40	.911	23.14	.889	22.58	1.148	29.16	.610	15.49	.619	15.72	.897	22.78

Dimensions in inches (millimeters) and are subject to change without notice.

© 2011 Glenair, Inc.

CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912

www.glenair.com

L-27

E-Mail: sales@glenair.com

11 - JULY - 2013